

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: OSRAM

Supplier's address: CQM contact, Berliner Alle 65, 86153 Augsburg, DE

Model identifier: LS_SHZ_600928

Type of light source:

Lighting technology used:	LED	Non-directional or directional:	NDLS
Light source cap-type (or other electric interface)	Leads, Soldering pads		
Mains or non-mains:	NMLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	Only with specific dimmers

Product parameters

Parameter	Value	Parameter	Value
-----------	-------	-----------	-------


General product parameters:

Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer		8	Energy efficiency class	F
Useful luminous flux (ϕ_{use}), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)		755 in Sphere (360°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	3 000
On-mode power (P_{on}), expressed in W		7,5	Standby power (P_{sb}), expressed in W and rounded to the second decimal	-
Networked standby power (P_{net}) for CLS, expressed in W and rounded to the second decimal		-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	80
Outer dimensions without separate control gear, light-	Height	1	Spectral power distribution in the range 250 nm to 800 nm, at full-load	See image in last page
	Width	8		
	Depth	500		


ing control parts and non-lighting control parts, if any (millimetre)				
Claim of equivalent power ^(a)	-	If yes, equivalent power (W)	-	
		Chromaticity coordinates (x and y)	0,432 0,399	
Parameters for LED and OLED light sources:				
R9 colour rendering index value	0	Survival factor	1,00	
the lumen maintenance factor	0,96			

(a) '-': not applicable;

(b) '-': not applicable;



Model placed on the Union market from 08/02/2022



EPREL registration number: 1152347

<https://eprel.ec.europa.eu/qr/1152347>

Supplier: Inventronics GmbH (Manufacturer)

Website: <https://www.inventronicsglobal.com/>

Customer care service:

Name: CQM contact

Website: www.inventronicsglobal.com

Email: cqm-emea@inventronicsglobal.com

Phone: +4962130

Address:

Berliner Alle 65
86153 Augsburg
Germany