

RP73PF1J976RBTDF

✓ ACTIVE

Holsworthy | Holsworthy RP73

TE Internal #: 1-2176088-2

976 ohm, Surface Mount Precision Resistor, Thin Film, 0603, .166 W,
.1 %, ±25 ppm/°C, Solder, 2 Terminations, .45 mm [.018 in] Height,
Holsworthy RP73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistance Value: 976 Ω
Resistor Type: Precision Resistor
Element Type: Thin Film
Package Size Code: 0603
Power Rating: .166 W

Features

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	0603

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	100 V
Resistance Value	976 Ω
Power Rating	.166 W
Resistance Class	Up to 1kΩ
Passive Component Tolerance	.1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.45 mm[.018 in]
Product Length	1.55 mm[.061 in]



Product Width	.8 mm[.031 in]
---------------	----------------

Usage Conditions

Temperature Coefficient	±25 ppm/°C
-------------------------	------------

Industry Standards

Moisture Sensitivity Level	1
----------------------------	---

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

RP73PF1J976RBTDF

976 ohm, Surface Mount Precision Resistor, Thin Film, 0603, .166 W, .1 %, ±25 ppm/°C, Solder, 2 Terminations, .45 mm [.018 in] Height, Holsworthy RP73



TE Part # 1625867-2
[RP 1J 0.166W 10K 0.1% 25PPM 1K RL](#)




TE Part # 2176308-5
[RP 1E 0.1W 147K 0.1% 25PPM 5K RL](#)



TE Part # 2176093-5
[RP 2A 0.25W 10K 0.1% 25PPM 1K RL](#)



TE Part # 1-2176092-8
[RP 2A 0.25W 1K0 0.1% 25PPM 1K RL](#)



TE Part # 2-2176308-7
[RP 1E 0.1W 249K 0.1% 25PPM 5K RL](#)

Also in the Series | [Holsworthy RP73](#)



[Surface Mount Resistors\(4227\)](#)

Customers Also Bought



TE Part #2176089-6
[RP 1J 0.166W 11K5 0.1% 25PPM 1K RL](#)



TE Part #34145
[PG R 22-16 COMM 22-18 MIL 8](#)



TE Part #7-1879497-3
[CRGH1206 5% 1K0 0.5W](#)



TE Part #3-2176156-3
[TLM 1206 0.5W R062 1% 50PPM 5K RL](#)



TE Part #9-1676480-8
[CRG0402 1% 10R](#)



TE Part #1622548-1
[LR1 1% 68K](#)



TE Part #1622296-1
[LR1 1% 100K](#)



TE Part #8-1676481-1
[CPF 0603 18K 0.1% 25PPM 1K RL](#)



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2176088-2_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2176088-2_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2176088-2_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RP73-0915

English