



Main

Range	Ovalis C Series
Product or component type	Cable outlet
Device presentation	Mechanism with fixing frame
Product specific application	Exit wire for electrical heating
Type of packing	Paint cover
Condition of use	Indoor

Complementary

Device mounting	Flush
Rated current	16 A
Fixing mode	By screws By claws
Colour tint	Anthracite (RAL 7021)
Surface finish	Matt
Connections - terminals	Screw terminals
Number of loop terminals	2
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1 x 1.5...1 x 2.5 mm ² for flexible cable(s) 1 x 1.5...1 x 2.5 mm ² for stranded cable(s)
Cable outer diameter	6...12 mm
Wire stripping length	12 mm
Material	Thermoplastic ABS-UV stabilised: centre plate PBT (polybutylene terephthalate) GF30: support frame
Height	87 mm
Width	87 mm
Depth	54 mm
Embedding depth	11.7 mm
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...35 °C
Standards	UTE C 61-392 EN 60669-1
Product certifications	LCIE: NF 603415A[RETURN]JNF
IK degree of protection	IK04

IP degree of protection	IP2XC
Environmental characteristic	Bleach Liquid soap Window-cleaning fluid Alcohol Acetone Oil UV resistant Petrol

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Minimum percentage of recycled plastic content	18