

# Product data sheet

Specifications



Repacked, miniature circuit breaker (MCB), Acti9 iC60L, 4P, 16A, C curve, 25kA (IEC/EN 60947-2)

A9F94416W



This repacked option saves 4.244 over the standard condition

## Main

|                           |                                                                      |
|---------------------------|----------------------------------------------------------------------|
| Range                     | Acti9                                                                |
| Product name              | Acti9 iC60                                                           |
| Product or component type | Miniature circuit-breaker                                            |
| Device short name         | iC60L                                                                |
| Device application        | Distribution                                                         |
| Poles description         | 4P                                                                   |
| Number of protected poles | 4                                                                    |
| [In] rated current        | 16 A                                                                 |
| Network type              | AC<br>DC                                                             |
| Trip unit technology      | Thermal-magnetic                                                     |
| Curve code                | C                                                                    |
| Utilisation category      | Category A conforming to EN/IEC 60947-2                              |
| Suitability for isolation | Yes conforming to EN/IEC 60947-2<br>Yes conforming to EN/IEC 60898-1 |
| Standards                 | EN/IEC 60947-2<br>EN/IEC 60898-1                                     |

## Complementary

|                                       |                                                                                                                                                                                                                                                                                                                                                                                                     |
|---------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Network frequency                     | 50/60 Hz                                                                                                                                                                                                                                                                                                                                                                                            |
| [Ue] rated operational voltage        | 12...133 V AC 50/60 Hz<br>220...240 V AC 50/60 Hz<br>380...415 V AC 50/60 Hz<br>440 V AC 50/60 Hz<br><= 250 V DC                                                                                                                                                                                                                                                                                    |
| Magnetic tripping limit               | 8 x In +/- 20 %                                                                                                                                                                                                                                                                                                                                                                                     |
| Breaking capacity                     | 70 kA Icu at 12...133 V AC 50/60 Hz conforming to EN/IEC 60947-2<br>50 kA Icu at 220...240 V AC 50/60 Hz conforming to EN/IEC 60947-2<br>25 kA Icu at 380...415 V AC 50/60 Hz conforming to EN/IEC 60947-2<br>20 kA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2<br>20 kA Icu at <= 250 V DC conforming to EN/IEC 60947-2<br>15000 A Icn at 400 V AC 50/60 Hz conforming to EN/IEC 60898-1 |
| [Ics] rated service breaking capacity | 35 kA 50 % x Icu at 12...133 V AC 50/60 Hz conforming to EN/IEC 60947-2<br>25 kA 50 % x Icu at 220...240 V AC 50/60 Hz conforming to EN/IEC 60947-2<br>12.5 kA 50 % x Icu at 380...415 V AC 50/60 Hz conforming to EN/IEC 60947-2<br>10 kA 50 % x Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2<br>20 kA 100 % x Icu at <= 250 V DC conforming to EN/IEC 60947-2                            |
| Limitation class                      | 3 conforming to EN/IEC 60898-1                                                                                                                                                                                                                                                                                                                                                                      |
| [Ui] rated insulation voltage         | 500 V AC 50/60 Hz conforming to EN/IEC 60947-2                                                                                                                                                                                                                                                                                                                                                      |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                                  |                                                                                                                                                                                                                                                                                                                                                                                         |
|--------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| [Uimp] rated impulse withstand voltage           | 6 kV conforming to EN/IEC 60947-2                                                                                                                                                                                                                                                                                                                                                       |
| Contact position indicator                       | Yes                                                                                                                                                                                                                                                                                                                                                                                     |
| Control type                                     | Toggle                                                                                                                                                                                                                                                                                                                                                                                  |
| Local signalling                                 | Trip indicator                                                                                                                                                                                                                                                                                                                                                                          |
| Mounting mode                                    | Clip-on<br>Removable comb busbar installed                                                                                                                                                                                                                                                                                                                                              |
| Mounting support                                 | 35 mm DIN rail                                                                                                                                                                                                                                                                                                                                                                          |
| Comb busbar and distribution block compatibility | Top or bottom: YES                                                                                                                                                                                                                                                                                                                                                                      |
| Connection pitch                                 | 18 mm between phases                                                                                                                                                                                                                                                                                                                                                                    |
| 9 mm pitches                                     | 8                                                                                                                                                                                                                                                                                                                                                                                       |
| Height                                           | 85 mm                                                                                                                                                                                                                                                                                                                                                                                   |
| Width                                            | 72 mm                                                                                                                                                                                                                                                                                                                                                                                   |
| Depth                                            | 78.5 mm                                                                                                                                                                                                                                                                                                                                                                                 |
| Product weight                                   | 0.5 kg                                                                                                                                                                                                                                                                                                                                                                                  |
| Colour                                           | White                                                                                                                                                                                                                                                                                                                                                                                   |
| Mechanical durability                            | 20000 cycles                                                                                                                                                                                                                                                                                                                                                                            |
| Electrical durability                            | 10000 cycles                                                                                                                                                                                                                                                                                                                                                                            |
| Connections - terminals                          | Single terminal (top or bottom) , for 1 cable(s) , 1...25 mm², rigid, copper<br>Single terminal (top or bottom) , for 1 cable(s) , 1...16 mm², flexible, copper<br>Single terminal (top or bottom) , for 1 cable(s) , 1...16 mm², flexible with ferrule, copper<br>Single terminal (top or bottom) , for 1.0 cable(s) , flexible, copper or aluminium, with ring terminal and accessory |
| Wire stripping length                            | 14 mm for top or bottom connection                                                                                                                                                                                                                                                                                                                                                      |
| Tightening torque                                | 2 N.m top or bottom                                                                                                                                                                                                                                                                                                                                                                     |
| Earth-leakage protection                         | Separate block                                                                                                                                                                                                                                                                                                                                                                          |

## Environment

|                                       |                                                                                                         |
|---------------------------------------|---------------------------------------------------------------------------------------------------------|
| IP degree of protection               | IP20 conforming to IEC 60529<br>IP40 in modular enclosure (Insulation class II) conforming to IEC 60529 |
| Pollution degree                      | 3 conforming to EN/IEC 60947-2                                                                          |
| Overvoltage category                  | IV                                                                                                      |
| Tropicalisation                       | 2 conforming to IEC 60068-1                                                                             |
| Relative humidity                     | 95 % at 55 °C                                                                                           |
| Operating altitude                    | 0...2000 m                                                                                              |
| Ambient air temperature for operation | -35...70 °C                                                                                             |
| Ambient air temperature for storage   | -40...85 °C                                                                                             |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 7.700 cm  |
| Package 1 Width              | 11.700 cm |
| Package 1 Length             | 15.700 cm |

|                              |           |
|------------------------------|-----------|
| Package 1 Weight             | 490.000 g |
| Unit Type of Package 2       | S02       |
| Number of Units in Package 2 | 6         |
| Package 2 Height             | 15.000 cm |
| Package 2 Width              | 30.000 cm |
| Package 2 Length             | 40.000 cm |
| Package 2 Weight             | 3.244 kg  |

## Contractual warranty

|                      |    |
|----------------------|----|
| Warranty (in months) | 18 |
|----------------------|----|



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Lower carbon footprint

4 kg CO2 eq.

## Use Better



### Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

26ff71d1-98cf-4280-8725-455b9a6b2fb9

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

## Use Longer



### Lifetime extension

Repair

No

## Use Again



### Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins