




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **6**

Number of Rows: **2**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Breakaway
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	6
Number of Rows	2
Board-to-Board Configuration	Parallel

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Shape & Form	Square
Contact Base Material	Copper Zinc



Termination Features

Termination Method to Printed Circuit Board	Surface Mount
---	---------------

Mechanical Attachment

Mating Alignment	Without
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
Housing Material	PCT

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Type	Carton
----------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 215307-3
2X3P HV100 REC CON. TE, 7.0MM

TE Part # 215309-3
2X3P HV100 REC CON. TE, 8.5MM

TE Part # 925367-3
MOD 4 REC.HSG 2X03P

TE Part # 969973-3
2x3P HV100 REC. CON, SMD, GOLD, BLISTER

TE Part # 216604-3
HV190 REC ASSY 2X 3P.

TE Part # 829264-3
2X 3P HV100 REC CON.B/TE, 6.2,NO KINK

Customers Also Bought

TE Part #1415898
RTS3T012

TE Part #878462-000
S1125-KIT-1

TE Part #280372-2
6P AMPMODU II SHRD HDR, ST, 0.38 AU

TE Part #1241050-2
2x2P MOD II BREAK AWAY HDR,SMD, BLISTER



TE Part #280371-2
4P AMPMODU II SHRD HDR, ST, 0.38
AU

TE Part #3-1437565-0
FSM2JSMATR=ON T/R

TE Part #5053194052
RNF-100-1/2-0-SP

TE Part #1393230-9
RP3SL012

TE Part #1551920-2
zQSFP+ connector assembly

Documents

Product Drawings

2X3P MODUII BREAK AWAY HEADER, SMD

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_966709-3_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_966709-3_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_966709-3_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

TE Material Declaration

English