




ITEM #	PART #	REV	DESCRIPTION	QTY	Material	Weight
1	MDA050	01	Nozzle body	1	Aluminium	10.4g
2	PA6053	02	Narrow Angle Valve Assy. - 1.2mm	1		5.3g
3	PA6048	03	Narrow Angle Spray Valve Cap	1	Aluminium	9.8
4	FOZ005	02	O Ring	1	Viton	0.1g



REL-03	FOZ028 & FOZ005 'O' Rings were removed to stop problems with air flow.	27/11/2009
REV.	DESCRIPTION	DATE

 THIS DRAWING AND THE INFORMATION IT CONTAINS IS THE PROPERTY OF POWER ADHESIVES AND IS CONFIDENTIAL. IT MUST NOT BE REPRODUCED EITHER WHOLLY OR IN PART. ALL RIGHTS IN RESPECT OF PATENTS, DESIGNS AND COPYRIGHTS ARE RESERVED.	MATERIAL		DRAWN	SteveE	DIMENSIONS ARE IN MM UNLESS OTHERWISE STATED  THIRD ANGLE	TOLERANCES UNLESS OTHERWISE STATED WHOLE NUMBERS ±0.5mm 1 DECIMAL PLACE ±0.3mm 2 DECIMAL PLACE ±0.1mm	SCALE 1:1
	FINISH		DATE				SHEET 1 OF 2
	COLOUR		ECR No.	00036	TITLE		
	NOTES			Narrow Spray Nozzle Assy. - 1.2mm			
				DWG. No.			
			A4	MPN - PA6045	REVISION		
					03		

1	2	3	4	5	6				
Technical data									
Type	Hot melt applicator nozzle								
Material composition	Aluminium, steel, music wire, viton rubber								
Weight	25.6g (0.90 oz)								
Thread size	3/8 UNF								
Nozzle hole size	1.2mm (0.05")								
Spring rate	0.73 N/mm (4.15 lb/inch)								
									
 THIS DRAWING AND THE INFORMATION IT CONTAINS IS THE PROPERTY OF POWER ADHESIVES AND IS CONFIDENTIAL. IT MUST NOT BE REPRODUCED EITHER WHOLLY OR IN PART. ALL RIGHTS IN RESPECT OF PATENTS, DESIGNS AND COPYRIGHTS ARE RESERVED.			MATERIAL		DRAWN	SteveE	DIMENSIONS ARE IN MM UNLESS OTHERWISE STATED	TOLERANCES UNLESS OTHERWISE STATED	SCALE 1:1
			FINISH		DATE		 THIRD ANGLE	WHOLE NUMBERS ±0.5mm 1 DECIMAL PLACE ±0.3mm 2 DECIMAL PLACE ±0.1mm	SHEET 2 OF 2
			COLOUR		ECR No.	00036			TITLE
			NOTES			Narrow Spray Nozzle Assy. - 1.2mm			
						DWG. No.		REVISION	
						A4		03	
1	2	3	4	5	6				