

# Oxygen (19.5 - 23.5%,) Carbon Monoxide (0.001% - 0.0999%) in balance Nitrogen

## Safety Data Sheet 50280

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Date of issue: 05/30/2015 Version: 1.0

### SECTION 1: Identification

#### 1.1. Identification

Product form : Mixture  
Product name : Oxygen (19.5 - 23.5%,) Carbon Monoxide (0.001% - 0.0999%) in balance Nitrogen  
Replaces ISC MSDS No. : 1810-0701, 1810-0719, 1810-1063, 1810-1352, 1810-1493, 1810-2163, 1810-2230, 1810-2301, 1810-2302, 1810-2303, 1810-2665, 1810-6005

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of the substance/mixture : Test gas/Calibration gas.

#### 1.3. Details of the supplier of the safety data sheet

U.S. Supplier: Industrial Scientific Corporation  
1 Life Way  
Pittsburgh, PA 15205-7500  
Phone (412) 788-4353  
TOLL-FREE 800-DETECTS  
Fax (412) 788-8353

MANUFACTURER: CALGAZ  
821 Chesapeake Drive  
Cambridge, MD 21613

#### 1.4. Emergency telephone number

Emergency number : CHEMTREC: 1-800-424-9300  
Internationally: 1-703-527-3887

### SECTION 2: Hazard(s) identification

#### 2.1. Classification of the substance or mixture

##### GHS-US classification

Compressed gas H280 - Contains gas under pressure; may explode if heated  
Full text of H-phrases: see section 16

#### 2.2. Label elements

##### GHS-US labeling

Hazard pictograms (GHS-US) :



GHS04

Signal word (GHS-US) : Warning  
Hazard statements (GHS-US) : H280 - Contains gas under pressure; may explode if heated  
Precautionary statements (GHS-US) : P410+P403 - Protect from sunlight. Store in a well-ventilated place

#### 2.3. Other hazards

No additional information available

#### 2.4. Unknown acute toxicity (GHS US)

Not applicable

### SECTION 3: Composition/Information on ingredients

#### 3.1. Substance

Not applicable

#### 3.2. Mixture

# Oxygen (19.5 - 23.5%,) Carbon Monoxide (0.001% - 0.0999%) in balance Nitrogen

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Name	Product identifier	%	GHS-US classification
Nitrogen	(CAS No) 7727-37-9	76.4001 - 80.499	Compressed gas, H280
Oxygen	(CAS No) 7782-44-7	19.5 - 23.5	Ox. Gas 1, H270 Compressed gas, H280
Carbon monoxide	(CAS No) 630-08-0	0.001 - 0.0999	Flam. Gas 1, H220 Compressed gas, H280 Acute Tox. 3 (Inhalation:gas), H331 Repr. 1A, H360 STOT RE 1, H372

Full text of H-phrases: see section 16

### SECTION 4: First aid measures

#### 4.1. Description of first aid measures

- First-aid measures after inhalation : Adverse effects not expected from this product.  
First-aid measures after skin contact : Adverse effects not expected from this product.  
First-aid measures after eye contact : Adverse effects not expected from this product.  
First-aid measures after ingestion : Ingestion is not considered a potential route of exposure.

#### 4.2. Most important symptoms and effects, both acute and delayed

- Symptoms/injuries after inhalation : Adverse effects not expected from this product.  
Symptoms/injuries after skin contact : Adverse effects not expected from this product.  
Symptoms/injuries after eye contact : Adverse effects not expected from this product.  
Symptoms/injuries after ingestion : Ingestion is not considered a potential route of exposure.  
Symptoms/injuries upon intravenous administration : Not known.  
Chronic symptoms : Adverse effects not expected from this product.

#### 4.3. Indication of any immediate medical attention and special treatment needed

If you feel unwell, seek medical advice. If breathing is difficult, give oxygen.

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

- Suitable extinguishing media : Use extinguishing media appropriate for surrounding fire.  
Unsuitable extinguishing media : Do not use water jet to extinguish.

#### 5.2. Special hazards arising from the substance or mixture

- Fire hazard : The product is not flammable.  
Explosion hazard : Product is not explosive. Heat may build pressure, rupturing closed containers, spreading fire and increasing risk of burns and injuries.  
Reactivity : None known.

#### 5.3. Advice for firefighters

- Firefighting instructions : In case of fire: Evacuate area. Fight fire remotely due to the risk of explosion. Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire.  
Protection during firefighting : Standard protective clothing and equipment (e.g., Self Contained Breathing Apparatus) for fire fighters. Do not enter fire area without proper protective equipment, including respiratory protection.  
Specific methods : Exposure to fire may cause containers to rupture/explode. Continue water spray from protected position until container stays cool. Move containers away from the fire area if this can be done without risk.

### SECTION 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

- General measures : Ensure adequate ventilation.

##### 6.1.1. For non-emergency personnel

- Protective equipment : Wear protective equipment consistent with the site emergency plan.  
Emergency procedures : Escape the danger area by the closest safe route. Close doors and windows of adjacent premises. Keep containers closed. Mark the danger area. Seal off low-lying areas. Keep upwind.

# Oxygen (19.5 - 23.5%,) Carbon Monoxide (0.001% - 0.0999%) in balance Nitrogen

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

### 6.1.2. For emergency responders

- Protective equipment : Standard protective clothing and equipment (e.g., Self Contained Breathing Apparatus) for fire fighters. Equip cleanup crew with proper protection.
- Emergency procedures : Evacuate and limit access. Ventilate area.

### 6.2. Environmental precautions

Try to stop release if safe to do so.

### 6.3. Methods and material for containment and cleaning up

- For containment : Try to stop release if safe to do so.
- Methods for cleaning up : Dispose of this material and its container in accordance with local regulations.

### 6.4. Reference to other sections

See also Sections 8 and 13.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

- Additional hazards when processed : Pressurized container: Do not pierce or burn, even after use. Use equipment rated for cylinder pressure. Close valve after each use and when empty.
- Precautions for safe handling : Do not handle until all safety precautions have been read and understood. Use only outdoors or in a well-ventilated area.
- Safe handling of the gas receptacle : Protect cylinders from physical damage; do not drag, roll, slide or drop. Do not remove or deface labels provided by the supplier for the identification of the cylinder contents.
- Safe use of the product : Only experienced and properly instructed persons should handle gases under pressure. Consider pressure relief device(s) in gas installations. Ensure the complete gas system was (or is regularly) checked for leaks before use. Do not remove or deface labels provided by the supplier for the identification of the cylinder contents. Use only properly specified equipment which is suitable for this product, its supply pressure and temperature. Contact your gas supplier if in doubt.
- Hygiene measures : Do not eat, drink or smoke when using this product.

### 7.2. Conditions for safe storage, including any incompatibilities

- Technical measures : Comply with applicable regulations.
- Storage conditions : Do not expose to temperatures exceeding 52°C (125°F). Keep container closed when not in use. Protect cylinder from physical damage. Store in well ventilated area.
- Incompatible products : None known.
- Incompatible materials : Flammable materials.
- Storage area : Store away from heat. Store in a well-ventilated place.

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

Carbon monoxide (630-08-0)		
ACGIH	ACGIH TWA (ppm)	25 ppm
OSHA	OSHA PEL (TWA) (mg/m <sup>3</sup> )	55 mg/m <sup>3</sup>
OSHA	OSHA PEL (TWA) (ppm)	50 ppm

### 8.2. Exposure controls

- Appropriate engineering controls : Ensure exposure is below occupational exposure limits. Provide adequate general and local exhaust ventilation. Systems under pressure should be regularly checked for leakages. Consider work permit system e.g. for maintenance activities.
- Hand protection : Wear working gloves when handling gas containers. 29 CFR 1910.138: Hand Protection.
- Eye protection : Wear safety glasses with side shields. 29 CFR 1910.133: Eye and Face Protection.
- Skin and body protection : Wear suitable protective clothing, e.g. - lab coats, coveralls or flame resistant clothing.
- Respiratory protection : None necessary during normal and routine operations. See Sections 5 & 6.
- Thermal hazard protection : None necessary during normal and routine operations.
- Environmental exposure controls : Refer to local regulations for restriction of emissions to the atmosphere. See section 13 for specific methods for waste gas treatment.

# Oxygen (19.5 - 23.5%,) Carbon Monoxide (0.001% - 0.0999%) in balance Nitrogen

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Other information : Wear safety shoes while handling containers. 29 CFR 1910.136: Foot Protection.

### SECTION 9: Physical and chemical properties

#### 9.1. Information on basic physical and chemical properties

Physical state	: Gas
Appearance	: Clear, colorless gas.
Color	: Colorless
Odor	: Odorless
Odor threshold	: No data available
pH	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: No data available
Flash point	: Not applicable - not flammable
Relative evaporation rate (butyl acetate=1)	: No data available
Relative evaporation rate (ether=1)	: Not applicable for gas-mixtures.
Flammability (solid, gas)	: See Section 2.1 and 2.2
Explosion limits	: Not applicable - not flammable
Explosive properties	: Not applicable - not flammable.
Oxidizing properties	: Supports combustion.
Vapor pressure	: No data available
Relative density	: No data available
Relative vapor density at 20 °C	: No data available
Molecular mass	: Not applicable for gas-mixtures.
Relative gas density	: Similar to air
Solubility	: No data available
Log Pow	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Viscosity	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available

#### 9.2. Other information

No additional information available

### SECTION 10: Stability and reactivity

#### 10.1. Reactivity

None known.

#### 10.2. Chemical stability

Stable under normal conditions.

#### 10.3. Possibility of hazardous reactions

Can form explosive mixtures with flammable materials.

#### 10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

#### 10.5. Incompatible materials

Flammable materials.

#### 10.6. Hazardous decomposition products

Under normal conditions of storage and use hazardous decomposition products should not be produced.

# Oxygen (19.5 - 23.5%,) Carbon Monoxide (0.001% - 0.0999%) in balance Nitrogen

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

### SECTION 11: Toxicological information

#### 11.1. Information on toxicological effects

Likely routes of exposure : Inhalation  
Acute toxicity : Not classified

Carbon monoxide (630-08-0)	
LC50 inhalation rat (ppm)	1880 ppm/4h
ATE US (gases)	1880.000 ppmV/4h

Oxygen (7782-44-7)	
LC50 inhalation rat (ppm)	800000 ppm/4h

Nitrogen (7727-37-9)	
LC50 inhalation rat (ppm)	820000 ppm/4h

Skin corrosion/irritation : Not classified  
Serious eye damage/irritation : Not classified  
Respiratory or skin sensitization : Not classified  
Germ cell mutagenicity : Not classified  
Carcinogenicity : Not classified

Reproductive toxicity : Not classified  
Specific target organ toxicity (single exposure) : Not classified

Specific target organ toxicity (repeated exposure) : Not classified

Aspiration hazard : Not classified

Symptoms/injuries after inhalation : Adverse effects not expected from this product.  
Symptoms/injuries after skin contact : Adverse effects not expected from this product.  
Symptoms/injuries after eye contact : Adverse effects not expected from this product.  
Symptoms/injuries after ingestion : Ingestion is not considered a potential route of exposure.  
Symptoms/injuries upon intravenous administration : Not known.  
Chronic symptoms : Adverse effects not expected from this product.

### SECTION 12: Ecological information

#### 12.1. Toxicity

No additional information available

#### 12.2. Persistence and degradability

Carbon monoxide (630-08-0)	
Persistence and degradability	Will not undergo hydrolysis. Not readily biodegradable. Not applicable for inorganic gases.

Oxygen (7782-44-7)	
Persistence and degradability	No ecological damage caused by this product.

Nitrogen (7727-37-9)	
Persistence and degradability	No ecological damage caused by this product.

#### 12.3. Bioaccumulative potential

Carbon monoxide (630-08-0)	
Log Pow	1.78
Bioaccumulative potential	Not expected to bioaccumulate due to the low log Kow (log Kow < 4). Refer to section 9.

Oxygen (7782-44-7)	
Log Pow	Not applicable for inorganic gases.
Bioaccumulative potential	No ecological damage caused by this product.

# Oxygen (19.5 - 23.5%,) Carbon Monoxide (0.001% - 0.0999%) in balance Nitrogen

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Nitrogen (7727-37-9)	
Log Pow	Not applicable for inorganic gases.
Bioaccumulative potential	No ecological damage caused by this product.

### 12.4. Mobility in soil

Carbon monoxide (630-08-0)	
Ecology - soil	Because of its high volatility, the product is unlikely to cause ground or water pollution.
Oxygen (7782-44-7)	
Ecology - soil	No ecological damage caused by this product.
Nitrogen (7727-37-9)	
Ecology - soil	No ecological damage caused by this product.

### 12.5. Other adverse effects

Effect on ozone layer	: No known effects from this product.
Effect on the global warming	: Contains greenhouse gas(es) not covered by 842/2006/EC.

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

Waste treatment methods	: Contact supplier if guidance is required. Do not discharge into any place where its accumulation could be dangerous. Ensure that the emission levels from local regulations or operating permits are not exceeded.
Waste disposal recommendations	: Refer to the CGA Pamphlet P-63 "Disposal of Gases" available at <a href="http://www.cganet.com">www.cganet.com</a> for more guidance on suitable disposal methods.

## SECTION 14: Transport information

### Department of Transportation (DOT)

In accordance with DOT	
Transport document description	: UN1956 Compressed gas, n.o.s. (Nitrogen, Oxygen), 2.2
UN-No.(DOT)	: UN1956
Proper Shipping Name (DOT)	: Compressed gas, n.o.s.
Transport hazard class(es) (DOT)	: 2.2 - Class 2.2 - Non-flammable compressed gas 49 CFR 173.115
Hazard labels (DOT)	: 2.2 - Non-flammable gas



DOT Packaging Non Bulk (49 CFR 173.xxx)	: 302;305
DOT Packaging Bulk (49 CFR 173.xxx)	: 314;315
DOT Symbols	: G - Identifies PSN requiring a technical name
DOT Packaging Exceptions (49 CFR 173.xxx)	: 306;307
DOT Quantity Limitations Passenger aircraft/rail (49 CFR 173.27)	: 75 kg
DOT Quantity Limitations Cargo aircraft only (49 CFR 175.75)	: 150 kg
DOT Vessel Stowage Location	: A - The material may be stowed "on deck" or "under deck" on a cargo vessel and on a passenger vessel.
Other information	: No supplementary information available.

### TDG

No additional information available

### Transport by sea

UN-No. (IMDG)	: 1956
---------------	--------

# Oxygen (19.5 - 23.5%,) Carbon Monoxide (0.001% - 0.0999%) in balance Nitrogen

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Proper Shipping Name (IMDG) : COMPRESSED GAS, N.O.S.  
Class (IMDG) : 2 - Gases

### Air transport

UN-No. (IATA) : 1956  
Proper Shipping Name (IATA) : COMPRESSED GAS, N.O.S.  
Class (IATA) : 2

## SECTION 15: Regulatory information

### 15.1. US Federal regulations

#### Carbon monoxide (630-08-0)

Listed on the United States TSCA (Toxic Substances Control Act) inventory

#### Oxygen (7782-44-7)

Listed on the United States TSCA (Toxic Substances Control Act) inventory

#### Nitrogen (7727-37-9)

Listed on the United States TSCA (Toxic Substances Control Act) inventory

### 15.2. International regulations

#### CANADA

#### Carbon monoxide (630-08-0)

Listed on the Canadian DSL (Domestic Substances List)

WHMIS Classification

Class A - Compressed Gas  
Class B Division 1 - Flammable Gas  
Class D Division 1 Subdivision A - Very toxic material causing immediate and serious toxic effects  
Class D Division 2 Subdivision A - Very toxic material causing other toxic effects

#### Oxygen (7782-44-7)

Listed on the Canadian DSL (Domestic Substances List)

WHMIS Classification

Class A - Compressed Gas  
Class C - Oxidizing Material

#### Nitrogen (7727-37-9)

Listed on the Canadian DSL (Domestic Substances List)

WHMIS Classification

Class A - Compressed Gas

### EU-Regulations

No additional information available

### National regulations

#### Carbon monoxide (630-08-0)

Listed on the AICS (Australian Inventory of Chemical Substances)  
Listed on IECSC (Inventory of Existing Chemical Substances Produced or Imported in China)  
Listed on the Japanese ENCS (Existing & New Chemical Substances) inventory  
Listed on the Korean ECL (Existing Chemicals List)  
Listed on NZIoC (New Zealand Inventory of Chemicals)  
Listed on PICCS (Philippines Inventory of Chemicals and Chemical Substances)  
Listed on the Canadian IDL (Ingredient Disclosure List)

#### Oxygen (7782-44-7)

Listed on the AICS (Australian Inventory of Chemical Substances)  
Listed on IECSC (Inventory of Existing Chemical Substances Produced or Imported in China)  
Listed on the Korean ECL (Existing Chemicals List)  
Listed on NZIoC (New Zealand Inventory of Chemicals)  
Listed on PICCS (Philippines Inventory of Chemicals and Chemical Substances)

#### Nitrogen (7727-37-9)

Listed on the AICS (Australian Inventory of Chemical Substances)  
Listed on IECSC (Inventory of Existing Chemical Substances Produced or Imported in China)  
Listed on the Korean ECL (Existing Chemicals List)  
Listed on NZIoC (New Zealand Inventory of Chemicals)  
Listed on PICCS (Philippines Inventory of Chemicals and Chemical Substances)

# Oxygen (19.5 - 23.5%,) Carbon Monoxide (0.001% - 0.0999%) in balance Nitrogen

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

### 15.3. US State regulations

Carbon monoxide (630-08-0)				
U.S. - California - Proposition 65 - Carcinogens List	U.S. - California - Proposition 65 - Developmental Toxicity	U.S. - California - Proposition 65 - Reproductive Toxicity - Female	U.S. - California - Proposition 65 - Reproductive Toxicity - Male	Non-significant risk level (NSRL)
No	Yes	No	No	

Carbon monoxide (630-08-0)
U.S. - Massachusetts - Right To Know List U.S. - New Jersey - Right to Know Hazardous Substance List U.S. - Pennsylvania - RTK (Right to Know) - Environmental Hazard List U.S. - Pennsylvania - RTK (Right to Know) List

Oxygen (7782-44-7)
U.S. - Massachusetts - Right To Know List U.S. - New Jersey - Right to Know Hazardous Substance List U.S. - Pennsylvania - RTK (Right to Know) List

Nitrogen (7727-37-9)
U.S. - Massachusetts - Right To Know List U.S. - New Jersey - Right to Know Hazardous Substance List U.S. - Pennsylvania - RTK (Right to Know) List

### SECTION 16: Other information

Indication of changes	: Revised safety data sheet in accordance with OSHA final rule on GHS implementation promulgated March 26, 2012.
Other information	: This Safety Data Sheet is offered pursuant to OSHA's Hazard Communication Standard, 29 CFR, 1910.1200. Other government regulations must be reviewed for applicability to this product.

Full text of H-phrases:

Acute Tox. 3 (Inhalation:gas)	Acute toxicity (inhalation:gas) Category 3
Compressed gas	Gases under pressure Compressed gas
Flam. Gas 1	Flammable gases Category 1
Ox. Gas 1	Oxidizing gases Category 1
Repr. 1A	Reproductive toxicity Category 1A
STOT RE 1	Specific target organ toxicity (repeated exposure) Category 1
H220	Extremely flammable gas
H270	May cause or intensify fire; oxidizer
H280	Contains gas under pressure; may explode if heated
H331	Toxic if inhaled
H360	May damage fertility or the unborn child
H372	Causes damage to organs through prolonged or repeated exposure

SDS US (GHS HazCom 2012)

*This Safety Data Sheet is offered pursuant to OSHA's Hazard Communication Standard, 29 CFR, 1910.1200. Other government regulations must be reviewed for applicability to this gas mixture. To the best of Calgaz's knowledge, the information contained herein is reliable and accurate as of this date; however, accuracy, suitability or completeness are not guaranteed and no warranties of any type, either express or implied, are provided. The information contained herein relates only to this specific product. If this gas mixture is combined with other materials, all component properties must be considered. Data may be changed from time to time. Be sure to consult the latest edition.*