



Main

Range of product	Odace
Aesthetic name	Styl
Product or component type	Socket-outlet
Device presentation	Complete product
Socket number	2
Type of packing	Paint cover
Number of terminals per pole	2

Complementary

Device mounting	Flush
Outlet poles configuration	2P + E
Cover type	With shutter
Outlet standard deviation	French
Fixing mode	By screws
Colour tint	White (RAL 9003)
Surface finish	Glossy
Rated current	16 A
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50 Hz
Service life in cycles	5000 cycles
Electrical durability	5000 cycles
Connections - terminals	Screw terminals
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1 x 1.5...2 x 4 mm ² for rigid cable(s) 1 x 1.5...2 x 4 mm ² for stranded cable(s) 1 x 1.5...2 x 4 mm ² for flexible cable(s)
Wire stripping length	12 mm
Material	ASA + PC: mechanism cover PC (polycarbonate) GF10 FR: casing Sheet metal: support frame
Height	126 mm
Width	85 mm
Depth	46 mm
Embedding depth	27.1 mm
Net weight	0.111 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for storage	-5...50 °C
Dielectric strength	2000 V
Ambient air temperature for operation	5...35 °C
Standards	NF C 61-314
Product certifications	LCIE: NF 604966
IK degree of protection	IK04
IP degree of protection	IP21D

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations