



TE Internal #: 1-1744429-6
PCB Mount Header, Vertical, Wire-to-Board, 6 Position, 3.96 mm [.156 in] Centerline, Partially Shrouded, Tin (Sn), Through Hole - Solder, Power
[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**
PCB Mount Orientation: **Vertical**
Connector System: **Wire-to-Board**
Number of Positions: **6**
Number of Rows: **1**

Features

Product Type Features

Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Partially Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Loaded Positions	5
Number of Power Positions	6
PCB Mount Orientation	Vertical
Number of Positions	6
Number of Rows	1

Electrical Characteristics

--	--



Operating Voltage	250 VDC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1 µm[39.37 µin]
Contact Mating Area Plating Material Thickness	3.04 µm[120 µin]
PCB Contact Termination Area Plating Material Thickness	3.04 µm[120 µin]
Contact Layout	Inline
Contact Mating Area Length	7.7 mm[.303 in]
Contact Base Material	Brass
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Tin (Sn)
Contact Type	Tab
Contact Current Rating (Max)	8 A

Termination Features

Termination Post & Tail Length	3.69 mm[.145 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Mating Retention Type	Locking Tab
Mating Retention	With
PCB Mount Alignment Type	Pegs
PCB Mount Retention	Without
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	Without

Housing Features

Housing Material	Nylon
Centerline (Pitch)	3.96 mm[.156 in]

Dimensions

Connector Width	8.6 mm[.339 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]



Connector Height	9.4 mm[.37 in]
Connector Length	23.76 mm[.935 in]

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Glow Wire Rating	GWT 750°C (Without Flame)
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Other

Position Locations Omitted	3
Number of Blocked Positions	1

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2020 (205) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability













Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products




will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 1-1744524-6 EP 06P HEADER ASY NO 2,4,5 PIN</p>	 <p>TE Part # 1744429-2 3.96 EP HDR ASSY 2P W/PEGS, GW</p>	 <p>TE Part # 1-1744524-5 EP 05P HEADER ASY NO 3,4 PINS</p>	 <p>TE Part # 1744429-7 3.96 EP HDR ASSY 7P W/PEGS, GW</p>
 <p>TE Part # 1744489-6 3.96 EP HDR ASSY 06P NO PEG, GW</p>	 <p>TE Part # 1744429-4 3.96 EP HDR ASSY 4P W/PEGS, GW</p>	 <p>TE Part # 1744524-6 EP 06P HEADER ASY NO 4 PIN</p>	 <p>TE Part # 1-1744429-9 3.96 EP HDR ASSY 9P W/PEGS, GW, NO PIN 3</p>
 <p>TE Part # 1744429-6 3.96 EP HDR ASSY 6P W/PEGS, GW</p>	 <p>TE Part # 1-1744429-0 3.96 EP HDR ASSY 10P W/PEGS, GW</p>	 <p>TE Part # 1744429-5 3.96 EP HDR ASSY 5P W/PEGS, GW</p>	 <p>TE Part # 1744429-9 3.96 EP HDR ASSY 9P W/PEGS, GW</p>

Customers Also Bought

 <p>TE Part #ASA158F12390235000 623 PLUG</p>	 <p>TE Part #EC9833-000 ZHD-SCE-3.2-50-S1-4</p>	 <p>TE Part #1-1415543-5 RTE44110</p>	 <p>TE Part #1614770-4 BDS 2 A 250 10R 10%</p>
---	--	--	---



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1744429-6_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1744429-6_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1744429-6_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English