



## PRODUCT-DETAILS

**SAMHL32/25M****32MM SS-TPE COAT CONDUIT 25M - WH****General Information**

<b>Extended Product Type:</b>	SAMHL32/25M
<b>Product ID:</b>	7TCA296030R0446
<b>EAN:</b>	5020963801556
<b>Catalog Description:</b>	32MM SS-TPE COAT CONDUIT 25M - WH
<b>Long Description:</b>	Liquidtight. Anti-Microbial Conduit, Conduit Size - Metric 32 Millimeters / US Trade Size 1 Inch, Outside Diameter 33.1mm, Inside Diameter 26.7mm, Static Bend Radius 144mm, IP40-IP69 Rating, Galvanised Steel Core, String Packed and Thermoplastic Jacket, Reel Length 25 Meters, White
<b>Display Name:</b>	SAMHL32/25M

**Additional Information**

<b>Product Main Type:</b>	Adaptaflex Flexible Cable Protection
<b>Application:</b>	Suitable for indoor splash zone areas or food processing equipment

**Ordering**

EAN: 5020963801556

UPC: 786210213019

---

## Dimensions

Outside Diameter: 33.1 mm

---

## Technical

Number of Batteries: 0

Color: White

Material: Galvanised Steel Core, String Packed and Thermoplastic Jacket

---

## Environmental

WEEE Category: Product Not in WEEE Scope

RoHS Information: Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

---

## Container Information

Package Level 1 Units: 1 piece

Package Level 1 EAN: 5020963801556

Package Level 1 Height: 10.62 in  
270 mm

Package Level 1 Depth / Length: 26.77 in  
680 mm

Package Level 1 Width: 26.77 in  
680 mm

---

## Certificates and Declarations

Declaration of Conformity - CE: 9AKK107492A9618

RoHS Declaration: 9AKK107992A8994

REACH Declaration: 9AKK107992A8994

---

## External Classifications and Standards

ETIM 8: EC001179 - Protective metallic hose

ETIM 9: EC001179 - Protective metallic hose

UNSPSC: 39131706

---

## Categories

---

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

