









This module (Item No. 750-666/000-104) features four power outputs (O1 ... O4) and four clock-sensitive inputs (I1 ... I4), enabling a functionally safe connection between fail-safe digital inputs and outputs. Thus, the module can automatically control its fail-safe digital outputs, allowing safety-related applications up to SIL 3 / PL e to be implemented without a safety controller.

The module has 30 virtual inputs and 30 virtual outputs, making it possible to receive additional virtual output values from a controller and to link this information to the fail-safe digital inputs. The internal logic is configured using the WAGO Safety Editor (SEDI).

The sensors can be supplied directly with 24 V, or fed by two differently clocked outputs (T1 ... T2). The inputs connect potential-free, emergency-off switches with contacts, safety interlock switches, mode selectors, as well as both safety sensors and semiconductor outputs (e.g., light barriers, PLC outputs). The power outputs switch both DC13 resistive and inductive loads.

Power output O1 can be operated in high-side switching mode, while power output O2 can be used in high-side or low-side switching mode. Both power outputs are single-channel. The module monitors short circuits, cross circuits and 24 V power supply from separate sources. Monitoring and other safety-relevant parameters—such as operating modes, test pulse deactivation, discrepancy times, and filter times—can be configured using WAGO-I/O-CHECK.

The configuration tool can be conveniently integrated into engineering systems supporting both CC2 and CC3 tool calling interfaces (TCI). The PROFIsafe address can be set using the DIP switch located on the side of the module, or via WAGO-I/O-CHECK.

The module can be operated without a secure controller and is fieldbus-independent, but also supports the PROFIsafe protocol V2.6 (PROFINET®). Field and system levels are electrically isolated. Individual safety modules can be arranged in any combination when configuring the fieldbus node.

If, for example, the cable length of the 24 V supply is greater than 3 m, a WAGO Filter Module or an appropriate external filter must be used for the 24 V power supply to protect the module against surge and burst (per IEC 61000-6-7 and marine applications). Additional information can be found in the product manual (available in German and English). This module (Item No. 750-666/000-104) has been evaluated by UL in accordance with UL/CSA 61010-1, UL/CSA 61010-2-201, and UL 121201, CSA-C22.2 No. 213 standards. The functional safety evaluation was performed by TÜV Rheinland in compliance with the specified standards.

General technical data	
Protocols	Fail-safe communication via PROFIsafe V2.6 (PROFINET®); Non-fail-safe communication (PROFINET®; with functional limitations)
Configuration options	Device address adjustable via DIP switch, WAGO Safety Editor 75x, or engineering software for the safety controller; Parameters adjustable via WAGO Safety Editor 75x or engineering software for the safety controller
Indicators	LEDs (A-D), green/red: Status/error I1 ... I4; LED (E), red: Module error; LED (F), red/green: Local bus communication; LED (G), red/green: Protocol status; LED (H), red/green: Parameterization; LED (I, K), red/green: Status/error O1 ... O2
Device specification	GSD specification: V2.4
Number of F I/O modules per node (fieldbus coupler/controller)	See information in the manual about the respective fieldbus coupler/controller
Device-specific	Channel-granular passivation: available; Safe logic: Up to 12 functions configurable; 30 virtual inputs and outputs via process image
Total number of channels (module)	6
Pluggable connector	fixed

Digital Inputs	
Number of digital inputs	4
Signal type	Digital
Signal type (voltage)	24 VDC
Sensor connection	4 x (Fail-safe input with test pulse)
Input characteristic	clock sensitive
Input characteristic	Type 1 per IEC 61131
Voltage range for signal (0)	-3 ... +5 VDC
Voltage range for signal (1)	15 ... 30 VDC
Input current per channel for signal (1) typ.	3 mA
Signal frequency (max.)	50 Hz
Input filter	0 ... 200 ms (parameterizable in steps)
Response times	See product manual
Minimum signal duration	= input filter time + test pulse duration + 2 ms

Digital Clock Outputs

Clock outputs	2
Signal type	Digital
Signal type (voltage)	24 VDC
Output current per channel	0.1 A
Test pulse duration (clock outputs)	Parameterizable between 0.5 ms and 200 ms in steps
Connection requirement (permissible cable length)	200 m
Connection requirement (permissible cable type)	Shielded or unshielded
Output protection (clock outputs)	Short circuit and overload protection

Digital Outputs

Number of digital outputs	2
Signal type	Digital
Signal type (voltage)	24 VDC
Output characteristic	Parameterizable test pulses
Output characteristics	10 ADC
Output current (per channel)	Resistive loads and general use: 10 ADC; Pilot duty and DC13: 2 ADC derating 1) per IEC 61010-1: 10 ADC $\leq 40^{\circ}\text{C}$, linearly decreasing to 6 ADC at 55°C derating 1) per UL 61010-1: 10 ADC $\leq 40^{\circ}\text{C}$, 6 ADC $\leq 55^{\circ}\text{C}$ 1) Temperature derating is unnecessary if a power-loss-free I/O module is connected to the right side of the F I/O Module (Item No. 750-666/000-104). See the product manual for a list of the I/O modules that can be used for this.
Output current (module)	10 A
Output residual current at signal "0"	< 1.0 mA
Output protection	Protected and short-circuit-proof per IEC 61131-2; Breaking capacity of the output protection: 1000 ADC If the power-supplying network provides a short-circuit current greater than the breaking capacity, a short circuit at the output may lead to the destruction of the F I/O module. Limitation of the inductive switching voltage: See product manual
Response threshold (output protection) min.	10.8 ADC
Response threshold (output protection) max.	15.6 ADC
Parallel connection of outputs	Not possible
Controlling an IEC 61131-2-compatible input	Possible; see product manual
Response times (max.) (outputs)	See product manual
Switching frequency (max.)	0.1 Hz; Capacitive load (with active discharge switched on)
Switching frequency (max.) (2)	0.1 Hz; Inductive load DC 13 (50 W) per IEC 60947-5-1, see product manual
Switching frequency (max.) (3)	50 Hz; Resistive load
Capacitive load for each channel	10,000 μF
Connection requirement (permissible cable length) (2)	200 m
Connection requirement (permissible cable type) (2)	Shielded or unshielded
Read-back time	1 ... 500 ms (parameterizable in steps)
Test pulse duration (digital outputs)	0 ... 500 ms; test pulse duration is adaptively adjusted to the actuator and corresponds to the read-back time at most.
Response threshold (output monitoring)min.	13.5 VDC (O1); Differential voltage between connections O2A and O2B: 4.0 ... 6.0 V
Response threshold (output monitoring) max.	16.0 VDC (O1)

Technical data

Supply voltage (system)	5 VDC; via data contacts
Current consumption (5 V system supply)	120 mA
Overvoltage category	II
Supply voltage (field)	24 VDC, SELV/PELV (-25 ... +30 %); For digital inputs; Power outputs: SELV/PELV 24 VDC (-25 ... +20 %) for inductive loads ("Pilot Duty" / DC13); SELV/PELV 24 VDC (-25 ... +30 %) for other applications; Current consumption from power outputs: 3 mA + load current
Current consumption, field supply (module with no external load)	30 mA
Isolation (peak value)	500 V output channel – output channel, system voltage, input channel
Number of incoming power jumper contacts	2
Number of outgoing power jumper contacts	2
Current carrying capacity (power jumper contacts)	10 A



Functional Safety	
Achievable safety classes	Logic: Cat. 4/PL e per ISO 13849; SIL 3 per IEC 61508 / EN 62061 Digital inputs and outputs (without clock outputs): Single-channel: Cat. 2/PL d per ISO 13849-1; SIL 2 per IEC 61508 / EN 62061; Dual-channel: Cat. 4/PL e per ISO 13849-1; SIL 3 per IEC 61508 / EN 62061
Safety standards	IEC 61508-1 ... -7; EN ISO 13849-1; EN 62061
Interface types according to ZVEI (inputs)	Drain; A, C0, C1, C2, C3
Interface types per ZVEI CB24I (outputs)	Source; C0, C1, C2, C3, D0, D1, D2, D3

Connection data	
Connection technology: I/O	16 x CAGE CLAMP®
Connectable conductor materials	Copper
Connection type	Inputs/outputs
Solid conductor	0.08 ... 2.5 mm² / 28 ... 14 AWG
Fine-stranded conductor	0.08 ... 2.5 mm² / 28 ... 14 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches

Physical data	
Width	24 mm / 0.945 inches
Height	100 mm / 3.937 inches
Depth	67.8 mm / 2.669 inches
Depth from upper-edge of DIN-rail	60.6 mm / 2.386 inches

Mechanical data	
Mounting type	DIN-35 rail
Pluggable connector	fixed

Material data	
Housing material	Polycarbonate; polyamide 6.6
Fire load	1.937 MJ
Weight	97.3 g
Conformity marking	CE; UKCA

Environmental requirements	
Ambient temperature (operation)	0 ... +55 °C
Ambient temperature (storage)	-40 ... +85 °C
Protection type	IP20
Protection class	III
Pollution degree	2 per IEC 61131-2
Operating altitude	0 ... 2000 m / 0 ... 6562 ft
Mounting position	Horizontal left, horizontal right, horizontal top, vertical top and vertical bottom
Relative humidity (without condensation)	95 %
Vibration resistance	4g per IEC 60068-2-6
Shock resistance	15g per IEC 60068-2-27
EMC immunity to interference	per EN 61000-6-2, marine applications, EN 61000-6-7 (FS)
EMC emission of interference	per EN 61000-6-4, marine applications, EN 61000-6-3
Exposure to pollutants	per IEC 60068-2-42 and IEC 60068-2-43
Permissible H ₂ S contaminant concentration at a relative humidity 75 %	10 ppm
Permissible SO ₂ contaminant concentration at a relative humidity 75 %	25 ppm



Commercial data	
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4066966509441
Customs tariff number	85371098990

Product Classification	
UNSPSC	32151705
ETIM 9.0	EC001599
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant,With Exemption
RoHS Exemption	6(c) 7(a) 7(c)-I 7(c)-II

Approvals / Certificates	
General approvals	Declarations of conformity and manufacturer's declarations



Approval	Standard	Certificate Name
UL Underwriters Laboratories Inc. (ORDINARY LOCATIONS)	-	E175199

Approval	Standard	Certificate Name
EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-

Approvals for marine applications		
-----------------------------------	--	--



Approval	Standard	Certificate Name
DNV DNV GL SE	DNV-CG-0339,Aug.2021	TAA0000194

Approvals for hazardous areas		
-------------------------------	--	--



Approval	Standard	Certificate Name
ATEX TUEV Nord Cert GmbH	EN 60079-0	TUEV14ATEX148929X (II 3 G Ex ec IIC T4 Gc)
IECEx TUEV Nord Cert GmbH	IEC 60079-0	IECEx TUN 14.0035 X (Ex ec IIC T4 Gc)
UL Underwriters Laboratories Inc. (HAZARDOUS LOCATIONS)	UL 121201	E198726

Approvals for functional safety		
---------------------------------	--	--



Approval	Standard	Certificate Name
Prod. Safety, Funct. Safety TUEV Rheinland Industrie Service GmbH	-	No. 968/EZ 247.18/21



Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance
750-666/000-104

↓

Documentation

Manual

Product Manual Fail-safe 4/2 channel digital input/output

2024-09-17
19.11.2024

pdf
6500.87 KB

↓

Bid Text

750-666/000-104

docx
41.50 KB

↓

750-666/000-104

x81
17.57 KB

↓

Instruction Leaflet

Gebrauchs- und Montageanleitung

V 1.0.0
26.02.2024

pdf
408.26 KB

↓

CAD/CAE-Data

CAD data

2D/3D Models
750-666/000-104

↓

1 Compatible Products

1.1 Optional Accessories

1.1.1 DIN-rail

1.1.1.1 Mounting accessories

 Item No.: 210-196 Aluminum carrier rail; 35 x 8.2 mm; 1.6 mm thick; 2 m long; unslotted; similar to EN 60715; silver-colored	 Item No.: 210-198 Copper carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715; copper-colored	 Item No.: 210-508 Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; galvanized; similar to EN 60715; silver-colored	 Item No.: 210-197 Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; similar to EN 60715; silver-colored
 Item No.: 210-506 Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; galvanized; similar to EN 60715; silver-colored	 Item No.: 210-114 Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; similar to EN 60715; silver-colored	 Item No.: 210-118 Steel carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715; silver-colored	 Item No.: 210-115 Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 18 mm; silver-colored
 Item No.: 210-112 Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 25 mm; silver-colored	 Item No.: 210-504 Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; galvanized; according to EN 60715; silver-colored	 Item No.: 210-113 Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; unslotted; according to EN 60715; silver-colored	 Item No.: 210-505 Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; unslotted; galvanized; according to EN 60715; silver-colored



1.1.2 Marking

1.1.2.1 Group marker carrier



[Item No.: 750-107](#)
Group marker carrier

1.1.2.2 Marker



[Item No.: 2009-145/000-006](#)
Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; blue



[Item No.: 2009-145/000-007](#)
Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; gray



[Item No.: 2009-145/000-023](#)
Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; green



[Item No.: 2009-145/000-012](#)
Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; orange



[Item No.: 2009-145/000-005](#)
Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; red



[Item No.: 2009-145/000-024](#)
Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; violet



[Item No.: 2009-145](#)
Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white



[Item No.: 2009-145/000-002](#)
Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; yellow



[Item No.: 248-501/000-006](#)
Mini-WSB marking card; as card; not stretchable; plain; snap-on type; blue



[Item No.: 248-501/000-007](#)
Mini-WSB marking card; as card; not stretchable; plain; snap-on type; gray



[Item No.: 248-501/000-023](#)
Mini-WSB marking card; as card; not stretchable; plain; snap-on type; green



[Item No.: 248-501/000-017](#)
Mini-WSB marking card; as card; not stretchable; plain; snap-on type; light green



[Item No.: 248-501/000-012](#)
Mini-WSB marking card; as card; not stretchable; plain; snap-on type; orange



[Item No.: 248-501/000-005](#)
Mini-WSB marking card; as card; not stretchable; plain; snap-on type; red



[Item No.: 248-501/000-024](#)
Mini-WSB marking card; as card; not stretchable; plain; snap-on type; violet



[Item No.: 248-501](#)
Mini-WSB marking card; as card; not stretchable; plain; snap-on type; white



[Item No.: 248-501/000-002](#)
Mini-WSB marking card; as card; not stretchable; plain; snap-on type; yellow

1.1.2.3 Marker carrier



[Item No.: 750-103](#)
Group marker carrier

1.1.3 Shield termination

1.1.3.1 Shield clamping saddles



[Item No.: 790-108](#)
Shield clamping saddle; 11 mm wide; diameter of compatible conductor; 3 ... 8 mm



[Item No.: 790-208](#)
Shield clamping saddle; 12.4 mm wide; 3 ... 8 mm



[Item No.: 790-116](#)
Shield clamping saddle; 19 mm wide; diameter of compatible conductor; 7 ... 16 mm



[Item No.: 790-216](#)
Shield clamping saddle; 21.8 mm wide; 6 ... 16 mm



[Item No.: 790-124](#)
Shield clamping saddle; 27 mm wide; diameter of compatible conductor; 6 ... 24 mm



[Item No.: 790-220](#)
Shield clamping saddle; 30 mm wide; 6 ... 20 mm



[Item No.: 790-140](#)
Shield clamping saddle; diameter of compatible conductor



1.1.4 Supply module

1.1.4.1 Supply module



Item No.: 750-612
Power Supply; 0 ... 230 V AC/DC



Item No.: 750-602
Power Supply; 24 VDC



Item No.: 750-601
Power Supply; 24 VDC; fuse holder



Item No.: 750-610
Power Supply; 24 VDC; fuse holder; Diagnostics

1.1.5 System enclosure

1.1.5.1 System enclosure



Item No.: 850-825
IP65 enclosure; Aluminium (RAL 7032); WxHxD (160x100x160 mm); 9 x M12, 4 x M20



Item No.: 850-826
IP65 enclosure; Aluminium (RAL 7032); WxHxD (240x100x160 mm); 4 x M20, 4 x M16, 14 x M12 cable grip



Item No.: 850-827
IP65 enclosure; Aluminium (RAL 7032); WxHxD (320x100x160 mm); 4 x M20, 8 x M16, 17 x M12 cable grip



Item No.: 850-828
IP65 enclosure; Aluminium (RAL 7032); WxHxD (480x100x160 mm); 4 x M20, 10 x M16, 35 x M12 cable grip



Item No.: 850-826/002-000
IP65 enclosure; Aluminium (RAL 7035); WxHxD (240x100x160 mm); 4 x M20, 4 x M16, 14 x M12 cable grip



Item No.: 850-827/002-000
IP65 enclosure; Aluminium (RAL 7035); WxHxD (320x100x160 mm); 4 x M20, 8 x M16, 17 x M12 cable grip



Item No.: 850-828/002-000
IP65 enclosure; Aluminium (RAL 7035); WxHxD (480x100x160 mm); 4 x M20, 10 x M16, 35 x M12 cable grip



Item No.: 850-834
IP65 enclosure; Polyester (RAL 7032); WxHxD (164x100x164 mm); 9 x M12, 4 x M20



Item No.: 850-835
IP65 enclosure; Polyester (RAL 7032); WxHxD (244x100x164 mm); 4 x M20, 4 x M16, 14 x M12 cable grip



Item No.: 850-836
IP65 enclosure; Polyester (RAL 7032); WxHxD (324x100x164 mm); 4 x M20, 8 x M16, 17 x M12 cable grip



Item No.: 850-814/002-000
IP65 enclosure; Sheet steel (RAL 7035); WxHxD (200x120x200 mm); without flange plate



Item No.: 850-815/002-000
IP65 enclosure; Sheet steel (RAL 7035); WxHxD (300x120x200 mm); without flange plate



Item No.: 850-816/002-000
IP65 enclosure; Sheet steel (RAL 7035); WxHxD (400x120x200 mm); without flange plate



Item No.: 850-817/002-000
IP65 enclosure; Sheet steel (RAL 7035); WxHxD (600x120x200 mm); without flange plate