

KERN JIT 200

KERN

Infrared thermometer for industry, environmental engineering and maintenance work



Category	
Brand	Sauter
Product category	Environment/ Occupational safety
Product group	Infrared thermometer
Product family	JIT

Measuring System	
Temperature - measuring range 1 [Min]	-32 °C
Temperature - measuring range 1 [Max]	0 °C
Temperature accuracy - measuring range 1	+/- 1,5 °C+0,1 °C/ °C
Temperature repeatability - measuring range 1	+/- 0,7 °C
Temperature coefficient - measuring range 1	+/- 0,1 °C/ °C
Temperature - measuring range 2 [Min]	0 °C
Temperature - measuring range 2 [Max]	100 °C
Temperature accuracy - measuring range 2	+/- 1,5 °C
Temperature repeatability - measuring range 2	+/- 0,7 °C
Temperature coefficient - measuring range 2	+/- 0,1 °C/ °C
Temperature - measuring range 3 [Min]	100 °C
Temperature - measuring range 3 [Max]	1020 °C
Temperature accuracy - measuring range 3	+/- 1,5%
Temperature repeatability - measuring range 3	+/- 0,7%

Temperature coefficient - measuring range 3	+/- 0,1% / °C
Level of emission [Min]	0,1
Level of emission [Max]	1
D:S Optic	20:1
Response time	250 ms
Default unit	°C
Units	°C °F
Temperature [Min] (°C)	-32 °C
Temperature [Max] (°C)	1100 °C

Construction	
Dimension (W×D×H)	179×127×53 mm
Material	plastic
Laser power	0,001 W
Laser class	2
Column mount possible	✓

Functions	
Function for averaging	✓
Limit-setting function	✓
Hold function	✓
Peak function	✓
Memory function	✓
Statistic function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	15 sec

Power Supply	
Supplied power supply	Battery
Battery / accumulator type	Alkali(-Manganese)
Battery	9 V block
Battery connection	9V Bloc
Battery operating time	9 h

Approval	
CE mark	✓
Packing & Shipping	
Delivery time	1 d
Dimensions packaging (W×D×H)	225×150×70 mm
Net weight	0,31 kg
Shipping method	Parcel service
Net weight approx.	0,35 kg
Gross weight approx.	0,50 kg
Shipping weight	0,5 kg

KERN JIT 200

KERN

Infrared thermometer for industry, environmental engineering and maintenance work

Pictograms

STANDARD

