

Shock absorber DYSD-Q13-7-5-Y1F-Y9

Part number: 8199040

FESTO



 General operating condition

Data sheet

Feature	Value
Size	7
Stroke	5 mm
Cushioning	Self-adjusting
Mounting position	Any
Position detection	None
Symbol	00991495
Max. impact speed	0.5 m/s
Reset time at room temperature	0.2 s
Reset time at min. ambient temperature	1 s
Mode of operation	Pushing Single-acting
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Ambient temperature	-10 °C ... 60 °C
Cushioning length	5 mm
Max. stop force	270 N
Max. tightening torque	3 Nm
Max. energy consumption per stroke	2.1 J
Max. energy consumption per hour	5040 J
Reset force	7 N
Min. insertion force	20 N
Product weight	20 g
Load range	16.8 kg
Type of mounting	Via lock nut
Note on materials	RoHS compliant
Material seals	NBR
Material housing	High-alloy steel
Material piston rod	High-alloy steel
Material nut	High-alloy steel