




Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Terminating Cover**

Number of Positions: **68**

Operating Temperature (Max): **105 °C [ 221 °F ]**

Operating Temperature Range: **-55 – 105 °C [ -67 – 221 °F ]**

Features

Product Type Features

|                      |                   |
|----------------------|-------------------|
| Connector Cover Type | Terminating Cover |
|----------------------|-------------------|

Configuration Features

|                     |    |
|---------------------|----|
| Number of Positions | 68 |
|---------------------|----|

Housing Features

|                                 |          |
|---------------------------------|----------|
| Compatible With Connector Shape | D-Shaped |
|---------------------------------|----------|

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature (Max) | 105 °C[221 °F]             |
| Operating Temperature Range | -55 – 105 °C[-67 – 221 °F] |

Industry Standards

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
|------------------------|----------|

Packaging Features

|                    |         |
|--------------------|---------|
| Packaging Method   | Package |
| Packaging Quantity | 1       |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|                                               |                                         |
|-----------------------------------------------|-----------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                               |
| EU ELV Directive 2000/53/EC                   | Compliant                               |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006        |                                         |



Current ECHA Candidate List: JAN 2025  
(247)  
Candidate List Declared Against: JAN 2025  
(247)  
Does not contain REACH SVHC

|                           |                                                |
|---------------------------|------------------------------------------------|
| Halogen Content           | Not Low Halogen - contains Br or Cl > 900 ppm. |
| Solder Process Capability | Not applicable for solder process capability   |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 749111-6  
68 50SR CABLE PLUG ASSY


Also in the Series | AMPLIMITE 0.50 Series



Connector Backshells(20)



Connector Caps & Covers(20)



D-Sub Backshells & Clamps(20)



Insertion & Extraction Tools(1)



PCB D-Sub Connectors(171)

Customers Also Bought



TE Part #HD16-9-96S-C016  
PLG, 9P, GRY, HJ BLK, THRD, 16



TE Part #HD36-24-35SN-059  
PLG,35P,AL,N, CBLCLMPBT,DRAIN,16 /20,S,MC



TE Part #207486-5  
SIZE 23-16 RECEPT,CPC,W/SEAL




TE Part #1579028-5  
EXTRACTION TOOL



TE Part #9-1768032-1  
LEB-0415P-4




TE Part #6-2176416-5  
9W STD M/OX 5% 24K




TE Part #554084-1  
PLUG ASSY,36 POS,BAIL LOCK,LPF



TE Part #1-1105001-2  
HD.M-C-BU.AU.0,3



TE Part #1977907-1  
CAT5e In-Line Shielded Coupler



TE Part #174928-5  
070 MLC W-W CAP HSG 3P BLUE

Documents

Product Drawings  
68 50SR CBL CONN TERM COVER

English

CAD Files  
3D PDF  
3D  
Customer View Model  
ENG\_CVM\_CVM\_749108-6\_J.2d\_dxf.zip



English

Customer View Model  
[ENG\\_CVM\\_CVM\\_749108-6\\_J.3d\\_igs.zip](#)

English

Customer View Model  
[ENG\\_CVM\\_CVM\\_749108-6\\_J.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications  
[Application Specification](#)

English

Instruction Sheets  
[CHAMPOMATOR 2.5 Terminating Machine Control Module 852423-\[ \]](#)

English