

Miniature circuit breaker 230/400 V 10kA, 1-pole, B, 16A, D=70 mm



Model	
Product brand name	SENTRON
Product designation	Miniature circuit breaker
General technical data	
Number of poles	1
Number of poles / Note	1P
Tripping characteristic class	B
circuit-breaker / Design	5SY4
Mechanical service life (switching cycles) / typical	10 000
Oversvoltage category	III
Voltage	
Insulation voltage	
<ul style="list-style-type: none"> with single-phase operation / at AC / rated value 	440 V
<ul style="list-style-type: none"> with multi-phase operation / at AC / rated value 	440 V
Supply voltage	
Type of voltage	AC
Current / at AC / rated value	16 A

Supply voltage	
<ul style="list-style-type: none"> • at AC / rated value 	400 V
Supply voltage frequency	
<ul style="list-style-type: none"> • rated value 	50/60 Hz
Protection class	
Protection class IP	IP20, with connected conductors
Switching capacity	
Switching capacity current	
<ul style="list-style-type: none"> • at DC / acc. to IEC 60947-2 / rated value 	15 kA
<ul style="list-style-type: none"> • acc. to EN 60898 / rated value 	10 kA
<ul style="list-style-type: none"> • acc. to IEC 60947-2 / rated value 	20 kA
Energy limiting class	3
Dissipation	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	1.8 W
Current	
Tripping residual / rated value / derated current / at 40 Cel	15.23 A
Suitability for operation	Mechanical engineering / industry
Product details	
Product function / neutral conductor switching	No
Product feature / Touch protection	Yes
Product component	
<ul style="list-style-type: none"> • combined terminal top 	Yes
<ul style="list-style-type: none"> • combined terminal bottom 	Yes
Product feature	
<ul style="list-style-type: none"> • Properties for main switches in accordance with EN 60204-1 	Yes
<ul style="list-style-type: none"> • halogen-free 	Yes
<ul style="list-style-type: none"> • sealable 	Yes
<ul style="list-style-type: none"> • silicon-free 	Yes
Product extension / can be installed / supplementary devices	Yes
Short circuit	
Breaking capacity short-circuit current (I _{cn})	
<ul style="list-style-type: none"> • at AC / acc. to UL 1077 and CSA C22.2 No.235 	5 kA
Connections	
<ul style="list-style-type: none"> • Connectable conductor cross-section 	
<ul style="list-style-type: none"> — solid 	0.75 ... 35 mm ²
<ul style="list-style-type: none"> — stranded 	0.75 ... 35 mm ²

<ul style="list-style-type: none"> Connectable conductor cross-section / finely stranded / with core end processing 	0.75 ... 25 mm ²
AWG number / as coded connectable conductor cross section	18 ... 4
Tightening torque [lbf·in] / with screw-type terminals	22 ... 31 lbf·in
Tightening torque / with screw-type terminals	2.5 ... 3.5 N·m
Position / of power supply cord	Any

Mechanical Design

Height	90 mm
Width	18 mm
Depth	76 mm
Installation depth	70 mm
Number of width units	1
Mounting type	Quick assembly system
Mounting position	any
Net weight	130 g

Environmental conditions

Ambient temperature	-40 ... +70 °C
<ul style="list-style-type: none"> during storage 	-40 ... +75 °C

Certificates

Reference code	
<ul style="list-style-type: none"> acc. to DIN EN 61346-2 	F
<ul style="list-style-type: none"> acc. to DIN EN 81346-2 	F

General Product Approval



CCC



IMQ



UR



VDE



RCM

[Miscellaneous](#)

Declaration of
Conformity

Test Certificates

Shipping Approval



EG-Konf.

[Special Test Certificate](#)

[Miscellaneous](#)



ABS



BUREAU
VERITAS

Lloyd's
Register

LRS

Shipping Ap-
proval

Railway



RINA

[Confirmation](#)

[Vibration and Shock](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SY4116-6>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SY4116-6>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SY4116-6

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



