

C40S4

circuit breaker basic frame, ComPacT
NSX400S, 100 kA at 415 VAC 50/60 Hz, 400
A, without trip unit, 4 poles



Main

Range	ComPacT new generation
Product name	ComPacT NSX new generation
Device short name	NSX400S
Product or component type	Basic frame
Device application	Distribution
Poles description	4P
Neutral position	Left
[In] rated current	400 A at 40 °C
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
Network type	AC
Network frequency	50/60 Hz
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Utilisation category	Category A
[Icu] rated ultimate short-circuit breaking capacity	100 KA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 120 KA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 40 KA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 65 KA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 90 KA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 25 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2
Performance level	S 100 kA 415 V AC
Control type	Toggle
Mounting mode	Fixed

Complementary

[Ui] rated insulation voltage	800 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-2
[Ics] rated service short-circuit breaking capacity	100 KA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 65 KA at 500 V AC 50/60 Hz conforming to IEC 60947-2 90 KA at 440 V AC 50/60 Hz conforming to IEC 60947-2 12 KA at 525 V AC 50/60 Hz conforming to IEC 60947-2 12 KA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 125 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical durability	15000 cycles conforming to IEC 60947-2
Electrical durability	12000 Cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2 3000 Cycles 690 V AC 50/60 Hz In conforming to IEC 60947-2 6000 Cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 6000 cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2
Mounting support	Backplate
Upside connection	Front
Downside connection	Front
Connection pitch	45 mm
Protection type	Without protection
Width (W)	185 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Height (H)	255 mm
Depth (D)	110 mm

Environment

Standards	EN/IEC 60947-2 UL 508
Product certifications	CSA UL
Pollution degree	3 conforming to IEC 60664-1
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14.5 cm
Package 1 Width	20.0 cm
Package 1 Length	29.5 cm
Package 1 Weight	5.898 kg
Unit Type of Package 2	P12
Number of Units in Package 2	28
Package 2 Height	45.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	181.0 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------