

LK-ALEV 127K-FI

Pressed steel swivel castor, Heavy duty design, with brake system 'stop-fix', heavy duty wheel, with 'Blickle EasyRoll' elastic solid rubber tyres, with aluminium wheel centre

EAN 4047526617691

ID 617696

Customs tariff number 87169090



Bracket: LK series

- strong pressed steel, zinc-plated, blue-passivated, Cr6-free
- double ball bearing in the swivel head
- strong central kingpin (from wheel Ø 125x50 mm)
- swivel head seal
- minimum swivel head play and smooth rolling characteristic and increased service life due to the special dynamic Blickle riveting process

Wheel: ALEV series

- tyre: high-quality elastic solid rubber "Blickle EasyRoll" in smooth rolling quality, hardness 65 Shore A, colour black
- wheel centre: die-cast aluminium

Other features:

- high chemical resistance to many aggressive substances, except oils
- operating temperature: -20 °C to +80 °C, temporarily up to +100 °C, reduced load capacity over +60 °C

Technical data:

Wheel Ø (D)	☉	125 mm
Wheel width	⊥	50 mm
Load capacity at 4 km/h	⚖	300 kg
Load capacity (static)	⚖	750 kg
Bearing type	⊙	ball bearing
Total height (H)	⊘	170 mm
Mounting type		top plate
Plate size	📏	140 x 110 mm
Bolt hole spacing	📏	105 x 75–80 mm
Bolt hole Ø	🔧	11 mm
Offset (F)	⊘	57 mm
Temperature resistance min		-20 °C
Temperature resistance max		70 °C
Tread and tyre hardness		65 Shore A
Unit weight	⚖	3.1 kg
Non-marking	✗	
Non-staining	✗	
Antistatic	⚡	✗
ESD	✗	
Electrically conductive	⚡	✗
Corrosion-resistant	✗	
Heat-resistant	🔥	✗
Suitable for autoclaves	✗	



Tread and tyre hardness

65 Shore A

Rolling resistance



very good

Wear resistance

good

Operating noise / floor surface preservation

very good



Product references



Corresponding fixed castor BH-ALEV 127K



Corresponding swivel castor LK-ALEV 127K



Wheel used ALEV 127/20K