


06800012

RCK 80 - Self centring

2D Technical Drawing

Dynamic 3D View
Technical Specifications

Part number (CODE)	06800012
Ød (DD) mm	12
ØD (D) mm	18
D1 (D1) mm	28
D2 (D2) mm	32
L1 (L1) mm	14
L2 (L2) mm	23.5
L3 (L3) mm	27.5
L (L) mm	31.5
Maximum torque Mt (MT) Nm	58
Clamping pressure - Shaft (CPS) N/mm ²	150
Clamping pressure - Hub (CPH) N/mm ²	100
Clamping screws DIN 912 MAT. 12.9 - Num. (CSN)	4
Clamping screws DIN 912 MAT. 12.9 - Type (CST)	M4x12
Clamping screws DIN 912 MAT. 12.9 - Torque (CSTQ) Nm	5.0