


FEATURES

- **Annealed Copper Conductor:** Enhances conductivity and durability
- **Polyvinyl Chloride Jacket:** Offers protection and flexibility
- **Plain Conductor Type:** Ensures consistent performance
- **24/0.2 Core Strands:** Provides flexibility and strength
- **3 Cores:** Suitable for a variety of electrical applications
- **Voltage Rating of 500 V:** Supports a wide range of electrical systems
- **Operating Temperature Range -15 °C to 70 °C:** Suitable for diverse environments
- **7.6 mm Outside Diameter:** Compact design for easy installation

RS PRO 0.75 mm² Flexible Cable, 100 m Length

RS Stock No: 606-136



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible cable is designed for reliable electrical connections in various industrial and commercial applications. With a conductor made from annealed copper, it ensures efficient conductivity and durability. The cable is suitable for installations requiring flexibility and resilience, providing a dependable solution for wiring needs.

General Specifications

| | |
|--------------------|-----------------|
| Conductor Material | Annealed Copper |
| Conductor Type | Plain |
| Jacket Colour | White |
| Product Type | Flexible Cable |

Mechanical Specifications

| | |
|------------------|----------------------|
| Cable CSA | 0.75 mm ² |
| Cable Length | 100 m |
| Core Strands | 24/0.2 |
| Jacket Material | Polyvinyl Chloride |
| Number of Cores | 3 |
| Outside Diameter | 7.6 mm |

Operation Environment Specifications

| | |
|-------------------------------|--------|
| Maximum Operating Temperature | 70 °C |
| Minimum Operating Temperature | -15 °C |

Approvals

| | |
|---------------------|---|
| Standards/Approvals | ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228 |
|---------------------|---|

Electrical Specifications

| | |
|---------|-------|
| Voltage | 500 V |
|---------|-------|