


602

CT 14

GREASE EP 2

MULTI-PURPOSE EXTREME PRESSURE LITHIUM GREASE



BENEFITS

- CT 14 contains extreme pressure, anti-wear and antioxidant free of heavy metals.
- CT 14 has significant adhesion to metals as well as good resistance to water and dust.
- This grease is the best value for money compared to standard "petroleum" greases that have no performance additives.
- This grease is "electrically insulating".



PQ 81600 : NATO G 414, DCEA 301
BOIENG D6-17487 R



72730020 (650/400 ml aerosol)
72730005 (800/500 ml aerosol)



DIN 51518 and 51825

DEFINITION

CT 14 is a high-quality, multi-purpose "lithium" grease thanks to its exceptional performance additives.

INSTRUCTIONS FOR USE

Clean and degrease parts before using CT14 grease.

CT 14 is pumpable. It can be applied by brush.

FEATURES

Color :	Light amber
Savo:	Lithium
Operating temperature:	-30 to +165°C
Dropping point (NFT 60-102):	185°C
NLGI Grade:	2
Penetration worked 60 cPs (NFT 60-132):	265-295
Anti-rust property (NFT 60-135):	cot 0
4-ball weld test (ASTM D 2596):	315 kg
DN factor:	> 350 000

ORAPI ® cannot be aware of all the applications in which its products are used and the conditions of their use. ORAPI ® assumes no responsibility for: the suitability of its products for a given use or for a particular purpose, the application methods over which it has no control. The information contained in this technical data sheet must in no case replace the preliminary tests that must be carried out to verify the suitability of the product for each intended application. The user of the product described in this technical data sheet remains solely responsible for all measures required to protect people and property against all risks that may result from the implementation and/or use of this product. Consequently, ORAPI ® disclaims all implied or explicit warranties, including warranties relating to the fitness for sale or suitability for a particular need, resulting from the sale or use of its products. ORAPI ® specifically denies any prosecution for incidental or consequential damages of any kind, including financial operating losses.

602

CT 14

GREASE EP 2

MULTI-PURPOSE EXTREME PRESSURE LITHIUM GREASE

FIELD OF APPLICATION

CT 14 is recommended for the following cases:

Ball and roller bearings, needles and rollers, bearings, chains, joints, construction and public works equipment, water treatment centers, lock joints, treatment plants, handling and transport equipment, agricultural equipment and all mechanisms under severe conditions, high loads, high temperatures, shock loads, humid and dusty ambient conditions.

PACKAGING

Fut 180 kg	ref. 3602 U1	x 1
Ton 50 kg	ref. 3602 O4	x 1
Ton 25 kg	ref. 3602 O2	x 1
Bucket 5 kg	ref. 3602 S1	x 4
Box 1 kg	ref. 3602 B7	x 6
Aerosol 800 / 500 ml	ref. 4602 A5	x 12
Aerosol 650 / 400 ml	ref. 4602 A4	x 12
Cartouche 400 g	ref. 3602 C4	x 12
Lube shuttle 400g	ref. 3602 CL	x 12
Tubes 100 g	ref. 3602 T3	x 12



ORAPI ® cannot be aware of all the applications in which its products are used and the conditions of their use. ORAPI ® assumes no responsibility for: the suitability of its products for a given use or for a particular purpose, the application methods over which it has no control. The information contained in this technical data sheet must in no case replace the preliminary tests that must be carried out to verify the suitability of the product for each intended application. The user of the product described in this technical data sheet remains solely responsible for all measures required to protect people and property against all risks that may result from the implementation and/or use of this product. Consequently, ORAPI ® disclaims all implied or explicit warranties, including warranties relating to the fitness for sale or suitability for a particular need, resulting from the sale or use of its products. ORAPI ® specifically denies any prosecution for incidental or consequential damages of any kind, including financial operating losses.