



# PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 10:19 (UTC)

MOTION & CONTROL  
**NSK**



## 21316EAE4

### Spherical Roller Bearings

#### Boundary Dimensions


d	80	mm	Bore diameter
D	170	mm	Outside diameter
B	39	mm	Width
r (min.)	2.1	mm	Chamfer dimension

#### Basic Load Ratings

Cr	355000	N	Basic dynamic load rating
C0r	375000	N	Basic static load rating

#### Speeds

Thermal Speed Rating (Oil-bath)	3800	min-1	Oil-bath lubrication subject to conditions outlined in ISO 15312
Mechanical (forced-circulation oil)	4800	min-1	Properly designed and controlled forced-circulation oil lubrication
Grease	3000	min-1	Grease lubrication
Oil (Oil-bath)	3800	min-1	Oil-bath lubrication



#### Abutment and Fillet Dimensions

da (min.)	92	mm	Diameter of shaft abutment
da (max.)	109	mm	Diameter of shaft abutment
Da (min.)	146	mm	Diameter of housing abutment
Da (max.)	158	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet

#### Calculation factors

e	0.23	Constant
Y2	4.4	Axial load Factors
Y3	3	Axial load Factors
Y0	2.9	Axial load Factors

#### Mass

Mass approx.	4.32	kg	Mass approx.
--------------	------	----	--------------

