




Part Number : [905841326](#)

Product Description : 1.27mm Pitch Picoflex PF-50
IDT Receptacle, Low Profile, Board-in, 26 Circuits

Series Number : 90584

Status : Active

Product Category : Connector Housings



Documents & Resources

Drawings

[905841326_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Specifications


[908140000-AS-000.pdf](#)

[PK-90584-001-001.pdf](#)

[PS-99020-0011-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	90584
Description	1.27mm Pitch Picoflex PF-50 IDT Receptacle, Low Profile, Board-in, 26 Circuits
Comments	Low Profile
Component Type	One Piece
Product Name	Picoflex
UPC	800753661790

Agency

UL	E29179
----	--------

Electrical

Voltage - Maximum	250V
-------------------	------

Physical

Circuits (Loaded)	26
Color - Resin	Natural
Durability (mating cycles max)	30

Entry Angle	90° Angle
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	1.583/g
Number of Rows	2
Packaging Type	Tube
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	1.27mm
Plating min - Mating	2.032µm
Plating min - Termination	2.032µm
Polarized to Mating Part	N/A
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole - Kinked Pin
Wire/Cable Type	Ribbon Cable
Wire Insulation Diameter	1.00mm max.
Wire Size (AWG)	26, 28

Solder Process Data

Lead-Free Process Capability	WAVE
------------------------------	------

Application Tooling

Global

Description	Part Number

PremiumGrade Hand Crimp Tool for Picoflex PF-50 IDT Receptacle, 4-26 Circuits, 28-26 AWG Flat Cable, 1.00mm max. Thickness	<u>690081090</u>
Arbor Press Fixture	<u>690201902</u>

This document was generated on Nov 10, 2025