



Twin Lens EAGLE Clear Mineral



FRAME

- Translucide Grilamid (plastic) frame with orbital protection
- Adjustable temples (length and inclination)
- Integrated side shields with ventilation system
- Rotating tips (perfect fitting)
- Clip-on available (full and half rim) for welding
- Available with prescription glasses
- Heat resistance : up to 90° C
- Weight : 44 g.

LENS

- Clear toughened mineral glass
- Optical quality class 1 (no distortion)
- Perfect resistance to chemical products
- Perfect resistance to scratch
- Resistance to reinforced solidity (12m/s)
- Visible Light Transmittance = 92%

FIELDS OF USE

- Abrasive environment (glass work industry...)
- Chemical environment
- Foundry (mold cleaning...)

DO NOT USE FOR

Does not protect against impact, liquid molten metal, laser beam, or any kind of welding application

FRAME MARKING

AOS EN166 - F CE

AOS = manufacturer AOSafety
 EN166 = n° of the standard
 F = low impact resistance (45m/s)
 CE = conformity marking

EUROPEAN STANDARD

This product conforms to the European Council Directive 89/686/EEC and with the EN166 :1995

EC-Type Examination Certificate
 N° 0070-683-085-08-02-0082

Issued by INRS (notified body n°0070)
 Avenue de Bourgogne - B.P. n°27
 54 501 Vandoeuvre Cedex, France
Conform to EN166



LENS MARKING

AOS . 1 . S

AOS = manufacturer AOSafety
 1 = optical class (permanent wear)
 S = reinforced solidity (12m/s)

PRODUCT REFERENCE

Size 59x13

Product Code	Frame	Lens	Material
02-3022-01			Toughened Mineral