

FEATURES

- Resistant to corrosion
- Available in various sizes
- Hard-wearing construction
- Single row radial ball bearing

15mm Deep Groove Ball Bearing 28mm O.D

RS Stock No.: 893-7468



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

A range of RS brand metric stainless steel deep groove, single row ball bearings that have been manufactured to withstand tough applications, moisture, corrosion and abrasion. Available in various sizes, ideal choice for the food and beverage industry due to the fact they are hygienic and have a high resilience to water.

General Specifications

Ball Bearing Type	Deep Groove
End Type	Sealed
Number of Rows	1
Static Load Rating	1.84kN
Material	Stainless Steel
Race Type	Plain
Bore Type	Parallel
Annelia	Pharmaceutical, Chemical, Medical, Printing, Engines/Pumps, Offshore/Marine, Food and Beverage
Application	Industry

Mechanical Specifications

Incide Diameter	15mm
Inside Diameter	15mm
Outside Diameter	28mm
Race Width	7mm
Dynamic Load Rating	3.44kN
Static Load	1.84kN
Mass	0.016Kg



