




Connectors > Automotive Connectors > Power Distribution Boxes > Other Hard Wired Boxes



Component Type: **Fuse Holder**

Number of Fuses (Maximum): **12**

Number of Fuses (Minimum): **12**

Number of Positions: **12**

Centerline (Pitch): **8.5 mm [.334 in]**

Features

Product Type Features

Component Type	Fuse Holder
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Fuses (Maximum)	12
Number of Fuses (Minimum)	12
Number of Positions	12

Housing Features

Centerline (Pitch)	8.5 mm[.334 in]
--------------------	-----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free




Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 880399-1
FUSE CONTACT




TE Part # 880398-2
FUSE CONTACT



TE Part # 880399-2
FUSE CONTACT




TE Part # 444442-2
RELAY ADAPTOR




TE Part # 880397-2
FUSE CONTACT


Customers Also Bought




TE Part #350200-1
.140 DIA SOK 14-10 PTPBR




TE Part #444017-1
HSG ASS'Y 9 POS JR



TE Part #2-962842-1
TAB 2.8x0.8 CONTACT CF SRC Sn



TE Part #880398-2
FUSE CONTACT



TE Part #880124
9 CIR PLUG 140DIA PANEL MT NAT




TE Part #880399-2
FUSE CONTACT



TE Part #444510-1
HSG 10P COMBINED



TE Part #444442-1
RELAY ADAPTOR 6POSN



TE Part #CAT-EC7491-T273
Econoseal Receptacles and Tabs

Documents

Product Drawings

HSG 12 POSN, FUSE CONTACT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_444312-1_F_c-444312-1-f.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_444312-1_F_c-444312-1-f.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_444312-1_F_c-444312-1-f.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.