

36 + 1 LED Battery Work Lamp AHL 361 IP 54 Dust & Splash proof IP 54.

- 2 step operation: Large light emitting surface with 36 extra-bright LEDs and special optics, additionally a single Power LED in the lamp head for extra-long operation.
- Integrated rechargeable NiMH battery. Charger and charging station included.
- Charge capacity: 100 - 240 V AC, 50 - 60 Hz.
- With a fully charged battery up to 4 hours operation with the large light, up to 12 hours with the single lamp head Power-LED.
- Shockproof casing with rubberised surface.
- 360° swivelled, retractable hanging hook and magnetised base for optimal attachment.
- ON/OFF switch.

Article No.	EAN-Code 4007123...	UP	Packaging	LEDs	Luminous flux	Measurements
1 17537 3	590889	1	Sales Box	36 + 1	36 LED: appr. 90 lm, 1 LED: appr. 24 lm	26 x 6 x 4,5 cm



ENTSPRICHT
ACCORDING TO
2009/125/EG

- With docking station; ideal for workshops, security etc.
Fully charged and ready for use when located in docking station.