



## Specification TEK402/TEK404 Continuity Tester



### Electrical

#### TEK402 Mk3

Probe voltage: 9V DC approx

Test current: 5mA

Continuity range (audible): up to 10k $\Omega$  nominal

Audible output level: 85dB minimum at 30cm with leads shorted

Overvoltage protection fuse rating: 50mA, 250V, Fast Acting Ceramic Fuse,  
20mm x 5mm

#### TEK404 Mk3

Probe voltage: 9V DC approx. (open circuit probe voltage) 4.6V DC (loaded)

Test current: <50 $\mu$ A (across short circuit)

Continuity range: 0 $\Omega$  to 2.2k $\Omega$   $\pm$  10%

Audible output level: 85dB minimum at 30cm with leads shorted

LED indication: bright orange LED Buzzer and LED intensity reduce with  
increasing continuity resistance.

Alarm function threshold: >30V  $\pm$  20V DC & AC rms

### Environmental

Temperature & humidity (Operating): -10 to 40°C at max 70% R.H.

(Storage): -10°C to 50°C  $\leq$  80% R.H.

Altitude: up to 2000m

Pollution degree 2

### General

Power: 9V, PP3 alkaline battery (IEC 6LR61, NEDA 1604A),

Dimensions: 150(H) x 64(W) x 31(D) mm.

Weight: TEK402 Mk3 approx 264g (including leads, croc clips & battery)



## Specification TEK402/TEK404 Continuity Tester

TEK404 Mk2 approx 296g (including leads, croc clips & battery)

Includes: TL49 test leads with uninsulated crocodile clips (TEK402 only), TL47 test leads with insulated crocodile clips (TEK404 only), 9V battery, instructions

### Safety

TEK402 Mk3 conforms to BS EN 61010-1, max 50 V to earth (no measurement category)

TEK404 Mk3 conforms to BS EN 61010-1 CAT III 600 V  
Class II, double insulation

### EMC

Conforms to BS EN 61326-1

### SPECIFICATION FOR TL47 & TL49 TEST LEADS

Maximum voltage: 1000V AC/DC Maximum current: 10A continuous

Connector: 4mm banana plug with fixed shroud

### Environmental

Temperature (operating & storage): 0°C to 40°C

Altitude: up to 2000m

Pollution degree 2

### Safety (TL47)

Conforms to BS EN 61010-031,

Probe tip caps fitted - CAT IV 600V, CAT III 1000V, 10A

Probe tip caps removed - CAT II 1000V, 10A

Crocodile clip fitted - CAT III 600V, CAT II 1000V, 10A

Class II, double insulation

### Safety (TL49)

Conforms to BS EN 61010-031,

Probe tip caps fitted - CAT III 1000V, 10A

Probe tip caps removed - CAT II 1000V, 10A

Crocodile clip fitted - Max 50 V to earth (no measurement category), 10A

Class II, double insulation

## Check out what else you can get from Martindale:

- 17th Edition Testers
- Accessories
- Calibration Equipment
- Continuity Testers
- Electricians' Kits
- Environmental Products
- Full Calibration & Repair Service
- Fuse Finders
- Digital Clamp Meters
- Digital Multimeters
- Labels
- Microwave Leakage Detectors
- Motor Maintenance Equipment
- Multifunction Testers
- Non-trip Loop Testers
- Pat Testers & Accessories
- Phase Rotation Testers
- Proving Units
- Socket Testers
- Thermometers & Probes
- Test Leads
- Voltage Indicators
- Specialist Metrohm Testers (4 & 5kV)
- Specialist Drummond Testers



Martindale Electric Company Limited  
Metrohm House, Imperial Park, Imperial Way,  
Watford, Hertfordshire, WD24 4PP, UK  
Tel: +44 (0)1923 441717 Fax: +44 (0)1923 446900  
E-mail: sales@martindale-electric.co.uk  
Website: www.martindale-electric.co.uk



© 2014 Martindale Electric Company Ltd.  
Registered in England No. 3387451. LIT400 Rev 8