

IL S3 BK DI8 DO4 2TX-PAC - Bus coupler



2692380

<https://www.phoenixcontact.com/in/products/2692380>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline, Bus coupler, Sercos, RJ45 jack, Digital inputs: 8, 24 V DC, connection technology: 3-conductor, Digital outputs: 4, 24 V DC, 500 mA, connection technology: 3-conductor, transmission speed in the local bus: 500 kbps / 2 Mbps, degree of protection: IP20, including inline connectors, marking fields, and end plate

Product description

The bus coupler with integrated I/Os is intended for use within a Sercos® network and represents the link to the Inline I/O system. Up to 63 Inline devices can be connected to the bus coupler. The bus coupler supports a maximum of 16 PCP devices. A corresponding SDDML file is available for integrating the Inline station into the programming system. This file can be downloaded at: phoenixcontact.net/product/2692380.

Your advantages

- 2 Ethernet ports
- Automatic detection of the transmission speed in the local bus (500 kbps or 2 Mbps)
- 8 digital inputs, 4 digital outputs (on-board)
- Minimum Sercos cycle time of 250 µs
- FSP-IO (Function Specific Profile-IO) for modular I/O devices
- Maximum of 6 realtime connections
- Hot plugging of participants in Sercos network
- Diagnostics trace
- Internet Protocol Services (IPS)
- Sercos specification V1.3.1
- Sercos diagnostic LED S and communication phase LED CP

Commercial data

Item number	2692380
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DRI
Product key	DRI11C
Catalog page	Page 103 (C-6-2019)
GTIN	4046356325882
Weight per piece (including packing)	343.6 g
Weight per piece (excluding packing)	298 g
Customs tariff number	85389091
Country of origin	DE

IL S3 BK DI8 DO4 2TX-PAC - Bus coupler




2692380

<https://www.phoenixcontact.com/in/products/2692380>

Technical data

Dimensions

Dimensional drawing	
Width	80 mm
Height	119.8 mm
Depth	71.5 mm
Note on dimensions	Specifications with connectors

Notes

Note on application	
Note on application	Only for industrial use

Interfaces

Sercos	
Number of interfaces	2
Connection method	RJ45 jack
Inline local bus	
Number of interfaces	1
Connection method	Inline data jumper
Transmission speed	500 kbps / 2 Mbps (automatic detection, no combined system)
Sercos	
Equipment type	Sercos slave

System properties

System limits	
Number of supported devices	max. 63 (per station)
Number of local bus devices that can be connected	max. 63
Number of devices with parameter channel	max. 16
Number of supported branch terminals with remote bus branch	0
Module	
ID code (hex)	none

Input data

Digital:	
----------	--

IL S3 BK DI8 DO4 2TX-PAC - Bus coupler



2692380

<https://www.phoenixcontact.com/in/products/2692380>

Input name	Digital inputs
Description of the input	EN 61131-2 type 1
Number of inputs	8
Connection method	Inline connector
Connection technology	3-conductor
Input voltage	24 V DC
Input voltage range "0" signal	-30 V DC ... 5 V DC
Input voltage range "1" signal	15 V DC ... 30 V DC
Nominal input voltage U_{IN}	24 V DC
Nominal input current at U_{IN}	typ. 3 mA
Typical input current per channel	typ. 3 mA
Typical response time	approx. 500 μ s
Protective circuit	Reverse polarity protection; Suppressor diode

Output data

Digital:

Output name	Digital outputs
Connection method	Inline connector
Connection technology	3-conductor
Number of outputs	4
Protective circuit	Short-circuit and overload protection; Freewheeling circuit in the output driver
Output voltage	24 V DC -1 V (At nominal current)
Maximum output current per module	max. 2 A
Nominal output voltage	24 V DC
Output voltage when switched off	max. 500 mV
Output current when switched off	max. 500 μ A (When not loaded, a voltage can be measured even at an output that is not set.)
Nominal load, inductive	12 VA (1.2 H, 48 Ω)
Nominal load, lamp	12 W
Nominal load, ohmic	12 W
Reverse voltage resistance to short pulses	Reverse voltage proof
Behavior with overload	Auto restart
Behavior with inductive overload	Output can be destroyed
Behavior at voltage switch-off	The output follows the power supply without delay
Signal delay	< 40 μ s (t_{on} , no load)
	< 50 μ s (t_{on} , load = 0.5 A)
	< 350 μ s (t_{off} , no load)
	< 235 μ s (t_{off} , load = 0.5 A)
Overcurrent shut-down	min. 0.7 A
Output current with ground connection interrupt when switched off	max. 25 mA

Product properties

IL S3 BK DI8 DO4 2TX-PAC - Bus coupler



2692380

<https://www.phoenixcontact.com/in/products/2692380>

Product type	I/O component
Product family	Inline
Type	modular
Scope of delivery	including inline connectors, marking fields, and end plate
No. of channels	12
Diagnostics messages	Short-circuit or overload of the digital outputs yes
	Sensor supply failure yes
	Failure of the actuator supply yes

Electrical properties

Maximum power dissipation for nominal condition	6.8 W
Protective circuit	Surge protection, protection against polarity reversal of the supply voltage; 35 V suppressor diode

Potentials: Bus coupler supply U_{BK} ; Communications power U_L (7.5 V) and the analog supply U_{ANA} (24 V) are generated from the bus coupler supply.

Supply voltage	24 V DC (via Inline connector)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 1 A (with max. number of connected I/O terminal blocks)
	typ. 60 mA (without connected I/O terminal blocks)

Potentials: Communications power (U_L)

Supply voltage	7.5 V DC
----------------	----------

Potentials: Supply of analog modules (U_{ANA})

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)

Potentials: Main circuit supply (U_M)

Supply voltage	24 V DC (via Inline connector)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 8 A
	min. 3 mA (without connected peripherals)

Potentials: Segment circuit supply (U_S)

Supply voltage	24 V DC (via Inline connector)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 8 A
	min. 3 mA (without connected peripherals)

Connection data

Connection technology

Connection name	Inline connector
-----------------	------------------

Conductor connection

Connection method	Spring-cage connection
Conductor cross section rigid	0.08 mm ² ... 1.5 mm ²

IL S3 BK DI8 DO4 2TX-PAC - Bus coupler



2692380

<https://www.phoenixcontact.com/in/products/2692380>

Conductor cross section flexible	0.08 mm² ... 1.5 mm²
Conductor cross section AWG	28 ... 16
Stripping length	8 mm

Inline connector

Connection method	Spring-cage connection
Conductor cross section, rigid	0.08 mm² ... 1.5 mm²
Conductor cross section, flexible	0.08 mm² ... 1.5 mm²
Conductor cross section AWG	28 ... 16
Stripping length	8 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Mounting

Mounting type	DIN rail mounting
	DIN rail mounting


IL S3 BK DI8 DO4 2TX-PAC - Bus coupler

2692380


<https://www.phoenixcontact.com/in/products/2692380>

Drawings

Connection diagram



Block diagram




IL S3 BK DI8 DO4 2TX-PAC - Bus coupler

2692380

<https://www.phoenixcontact.com/in/products/2692380>



Dimensional drawing





IL S3 BK DI8 DO4 2TX-PAC - Bus coupler

2692380

<https://www.phoenixcontact.com/in/products/2692380>



Dimensional drawing



IL S3 BK DI8 DO4 2TX-PAC - Bus coupler



2692380

<https://www.phoenixcontact.com/in/products/2692380>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/2692380>



EAC-RoHS

Approval ID: RU*-DE*HB.B.00386/20



EAC

Approval ID: TR_TS_D_00850-20



UL Listed

Approval ID: FILE E 140324



cUL Listed

Approval ID: FILE E 140324

cULus Listed

IL S3 BK DI8 DO4 2TX-PAC - Bus coupler



2692380

<https://www.phoenixcontact.com/in/products/2692380>

Classifications

ECLASS

ECLASS-11.0	27242608
ECLASS-12.0	27242608
ECLASS-13.0	27242608

ETIM

ETIM 9.0	EC001604
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

2692380

<https://www.phoenixcontact.com/in/products/2692380>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	304c9b95-6ddf-430e-8bc3-3711d6286f17

IL S3 BK DI8 DO4 2TX-PAC - Bus coupler



2692380

<https://www.phoenixcontact.com/in/products/2692380>

Accessories

CLIPFIX 35 - End bracket

3022218

<https://www.phoenixcontact.com/in/products/3022218>



Quick mounting end clamp for NS 35/7,5 DIN rail or NS 35/15 DIN rail, with marking option, width: 9.5 mm, color: gray

E/UK - End bracket

1201442

<https://www.phoenixcontact.com/in/products/1201442>



End bracket, Mounting on a DIN rail NS 32 or NS 35, material: PA, color: gray

IL S3 BK DI8 DO4 2TX-PAC - Bus coupler

2692380

<https://www.phoenixcontact.com/in/products/2692380>



IB IL SCN-PWR IN-CP - Inline connector

2727637

<https://www.phoenixcontact.com/in/products/2727637>



Connector, colored, for Inline power and segment terminal blocks

IL BKDIO-PLSET - Connector set

2878599

<https://www.phoenixcontact.com/in/products/2878599>



Connector set, for Inline bus coupler with I/Os mounted in rows

IL S3 BK DI8 DO4 2TX-PAC - Bus coupler

2692380

<https://www.phoenixcontact.com/in/products/2692380>



IB IL FIELD 8 - Marking field

2727515

<https://www.phoenixcontact.com/in/products/2727515>

Marking field, width: 48.8 mm



EMT (62X46)R - Insert label

0800059

<https://www.phoenixcontact.com/in/products/0800059>



Insert label, for marking Inline modules from Phoenix Contact, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, mounting type: insert, Number of individual labels: 250, text field height: 46 mm, text field width: 62 mm

IL S3 BK DI8 DO4 2TX-PAC - Bus coupler

2692380

<https://www.phoenixcontact.com/in/products/2692380>



IB IL FIELD 2 - Marking field

2727501

<https://www.phoenixcontact.com/in/products/2727501>

Marking field, width: 12.2 mm



EMT (62X10)R - Insert label

0800057

<https://www.phoenixcontact.com/in/products/0800057>



Insert label, for marking Inline modules from Phoenix Contact, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, mounting type: insert, Number of individual labels: 500, text field height: 10 mm, text field width: 62 mm

IL S3 BK DI8 DO4 2TX-PAC - Bus coupler

2692380

<https://www.phoenixcontact.com/in/products/2692380>



FL PLUG RJ45 GR/2 - RJ45 connector

2744856

<https://www.phoenixcontact.com/in/products/2744856>



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: Plastic, connection method: Crimp connection, connection cross section: AWG 26- 24, cable outlet: straight, color: gray, Ethernet

FL PLUG RJ45 GN/2 - RJ45 connector

2744571

<https://www.phoenixcontact.com/in/products/2744571>



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: Plastic, connection method: Crimp connection, connection cross section: AWG 26- 24, cable outlet: straight, color: green, Ethernet

IL S3 BK DI8 DO4 2TX-PAC - Bus coupler

2692380

<https://www.phoenixcontact.com/in/products/2692380>



FL CAT5 HEAVY - Data cable

2744814

<https://www.phoenixcontact.com/in/products/2744814>



CAT5-SF/UTP cable (J-02YS(ST)C HP 2 x 2 x 24 AWG), heavy-duty installation cable, 2 x 2 x 0.22 mm², solid conductor, shielded, outer sheath: 7.8 mm diameter, inner sheath: 5.75 mm ± 0.15 mm diameter

FL CAT5 FLEX - Installation cable

2744830

<https://www.phoenixcontact.com/in/products/2744830>



By the meter, Installation cable, Ethernet CAT5 (100 Mbps), shielded, PUR halogen-free, water blue RAL 5021, 4-wire (2x2xAWG26/7, SF/UTP), color single wire: white/orange-orange, white/green-green, cable length: Free entry (1.0 ... 1000.0 m)

IL S3 BK DI8 DO4 2TX-PAC - Bus coupler

2692380

<https://www.phoenixcontact.com/in/products/2692380>



FL CRIMPTOOL - Assembly tool

2744869

<https://www.phoenixcontact.com/in/products/2744869>

Crimping pliers, for assembling the RJ45 plugs FL PLUG RJ45..., for assembly on site



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in