

WINDOW-TYPE CURRENT TRANSFORMER, CLASS 1 300A/5A, 5VA PRIMARY CURRENT 300A, 5VA




Figure similar

Model		
Product designation		Window-type current transformers
Protection class		
Protection class IP		IP20
Connections		
Type of electrical connection / at output		screw-type terminals
Mechanical Design		
Height	mm	85.5
Width	mm	64
Width		
<ul style="list-style-type: none"> • of the push-through bus bar / at 1 bus bar / maximum 	mm	30
<ul style="list-style-type: none"> • of the push-through bus bar / in case of 2 bus bars / maximum 	mm	25
Depth	mm	80
Mounting type		screw fixing

Outer diameter / of the push-through conductor / maximum	mm	28
--	----	----

Environmental conditions

Ambient temperature		
• during operation / minimum	°C	-10
• during operation / maximum	°C	55

Certificates

Equipment marking / acc. to DIN EN 61346-2		T
--	--	---

General Product Approval	Declaration of Conformity
---------------------------------	----------------------------------



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/4NC5224-2CE20>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/4NC5224-2CE20/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=4NC5224-2CE20

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

09/05/2016