


# E40476



## Welding adapters EN10357 series A

ADAPT EN10357 DN100



EC 1935/2004 FCM FDA

### Application

Design	for volumetric flow meters SMF	
Application	food and beverage industry; hygienic systems	
Pressure rating	25 bar	2.5 MPa

### Tests / approvals

Pressure Equipment Directive	A possible classification to PED depends on the application and has to be carried out by the user / operator.
Safety instructions	The compatibility between medium and product material has to be checked in all applications.

### Mechanical data

Weight	[g]	4840.9
Materials		stainless steel (316L/1.4404)
Nominal diameter		DN100 (4")
Sensor connection		ifm-specific device flange
Process connection		welding adapter EN10357 series A (DIN)

# E40476



## Welding adapters EN10357 series A

ADAPT EN10357 DN100

Process connection suitable for pipe standard	(DIN EN 10357 series A); (DIN 11866 series A); (DIN 11850 series 2)
Surface characteristics Ra/Rz of the wetted parts	Ra ≤ 0.4 μm
<b>Accessories</b>	
Items supplied	screws 12
<b>Remarks</b>	
Pack quantity	2 pcs.