



PART NUMBER			SPECIFICATIONS					
BLACK OXIDE STEEL	ALUMINUM	STAINLESS STEEL	BORE B (mm)	OUTER DIAM. OD (mm)	SCREW LOCATION S (mm)	CLEARANCE DIAMETER C (mm)	WIDTH W (mm)	FORGED CLAMP SCREW
MWCL-6-F	MWCL-6-A	MWCL-6-SS	6	16	5,51	20,8	20	M3
MWCL-8-F	MWCL-8-A	MWCL-8-SS	8	18	6,5	22,4	20	M3
MWCL-10-F	MWCL-10-A	MWCL-10-SS	10	24	8,51	26,3	20	M3
MWCL-12-F	MWCL-12-A	MWCL-12-SS	12	28	10,01	32	24	M4
MWCL-16-F		MWCL-16-SS	16	34	12,5	39,3	29	M5
MWCL-20-F		MWCL-20-SS	20	40	14,73	47,4	33	M6
MWCL-25-F		MWCL-25-SS	25	45	17,5	52,1	33	M6
MWSP-6-F		MWSP-6-SS	6	16	5,51	20,8	20	M3
MWSP-8-F		MWSP-8-SS	8	18	6,5	22,4	20	M3
MWSP-10-F		MWSP-10-SS	10	24	8,51	26,3	20	M3
MWSP-12-F		MWSP-12-SS	12	28	10,01	32	24	M4
MWSP-16-F		MWSP-16-SS	16	34	12,5	39,3	29	M5
MWSP-20-F		MWSP-20-SS	20	40	14,73	47,4	33	M6
MWSP-25-F		MWSP-25-SS	25	45	17,5	52,1	33	M6

- Does not mar the shaft.
- Single point faced.
- Opposing hardware on 2-piece styles for balance.
- Excellent for high axial loads.
- Transmit torque in confined spaces.
- Step bores available.
- Bore tolerance: +.05mm  
-.00mm
- Additional sizes available.