

KEMET Part Number: PME278RE6100MR30
(P278EJ104M440A)

PME278/P278, Film, Metallized Paper, Safety, 0.1 uF, 20%, 440 VAC (X1), 1000 VDC, 110°C, Lead Spacing = 25.4mm



Dimensions

L	30.5mm MAX
H	19mm MAX
T	12.1mm MAX
S	25.4mm +/-0.4mm
LL	30mm +5mm
F	1mm +/-0.05mm

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	100

General Information

Supplier:	KEMET
Series:	PME278/P278
Dielectric:	Metallized Paper
Style:	Radial
Features:	EMI Safety
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	ENEC
AEC-Q200:	No
Construction:	Molded
Miscellaneous:	SRF= 3.9 MHz
Notes:	Not For New Design, Please Use The New P278 Series @ 480 VAC

Specifications

Capacitance:	0.1 uF
Capacitance Tolerance:	20%
Voltage AC:	440 VAC (X1)
Voltage DC:	1000 VDC
Temperature Range:	-40/+110C
Rated Temperature:	110°C
Dissipation Factor:	1.3% 1kHz
Insulation Resistance:	12 GOhms
Max dV/dt:	600 V/us
Safety Class:	X1