


Product description	M12 Male cable connector, Contacts: 8, shielded, moulded on the cable, IP67, UL 2238, PUR, black, 8 x 0.25 mm², 2 m
Area	M12-A
Coding	A-coded
Series	763
Part no.	77 3529 0000 50708-0200


Illustration



Scale drawing



Contact arrangement (Plug-in side)



Cable length tolerance

<i>cable length</i>	<i>tolerance</i>
≥ 0,10 m	+ 0,03 m
≥ 0,20 m	+ 0,04 m
≥ 0,50 m	+ 0,07 m
≥ 1,00 m	+ 0,10 m
≥ 2,00 m	+ 0,15 m
≥ 5,00 m	+ 0,20 m
≥ 10,0 m	+ 0,25 m
≥ 20,0 m	+ 0,35 m

Technical data

General features

Part no.	77 3529 0000 50708-0200
	Alternative part no.: 79 3579 32 08
Notice	Please note that, due to the change from the old to the new order number, there may be deviations in the technical specifications. For questions about product details, please use the 'Contact Customer Service' form on the right.
Connector design	Male cable connector
Type standard	DIN EN 61076-2-101
Coding	A-coded
Cable length	2 m (Standard 2 m and 5 m. Other lengths are available on request.)
Version	Connector pin straight
Connector locking system	screw
Termination	moulded on the cable
Degree of protection	IP67
Connection cross-section	0.25 mm ² / AWG 24

Product description	M12 Male cable connector, Contacts: 8, shielded, moulded on the cable, IP67, UL 2238, PUR, black, 8 x 0.25 mm², 2 m
Area	M12-A
Coding	A-coded
Series	763
Part no.	77 3529 0000 50708-0200

Temperature range from/to	-25 °C / 90 °C
Mechanical operation	> 100 Mating cycles
Weight (g)	230.9
Customs tariff number	85444290
Country of Origin	DE

Electrical parameters

Rated voltage	30 V
Rated voltage UL	2457
Rated impulse voltage	800 V
Rated current	2.0 A
Insulation resistance	$\geq 10^{10} \Omega$
Pollution degree	3
Overvoltage category	II
Insulating material group	II
EMC compliance	shielded
Shield connection	Shield on the threaded ring

Material

Housing material	PUR
Contact body material	PUR
Contact material	CuZn (brass)
Contact plating	Au (gold)
Locking material	CuZn (brass)
REACH SVHC	CAS 7439-92-1 (Lead)
SCIP number	8dfac39c-7f6c-4952-bdf1-d5dc3048cee0

Cable data - Structure of the cable

Cable diameter	6.0 mm
Cross section	8 x 0.25 mm ²
Sheath material	PUR
Single-lead insulation	PP9Y halogen-free
Single-lead structure	32 x 0.10 mm
Cable color	black

Cable data - Electrical properties

Conductor resistance	79 Ω /Km (20°C)
----------------------	------------------------

Cable data - Mechanical properties

Bending radius, fixed cable	$\geq 5 \times \emptyset$
Bending radius, moving cable	$\geq 10 \times \emptyset$
Bending cycles	> 2 million
Permitted acceleration	5 m/s ²

Product data sheet

Automation technology - Sensors and actuators



Product description **M12 Male cable connector, Contacts: 8, shielded, moulded on the cable, IP67, UL 2238, PUR, black, 8 x 0.25 mm², 2 m**

Area **M12-A**
Coding **A-coded**
Series **763**
Part no. **77 3529 0000 50708-0200**

Travel distance, horizontal	5 m/s ² -> 5 m
Travel distance, vertical	5 m/s ² -> 2 m
Travel speed	≤ 200 m/min (5 m horizontal distance)

Cable data - Thermal properties

Temperature range cable in move from/to	-25 °C / 90 °C
Temperature range cable fixed from/to	-50 °C / 90 °C

Cable data - Other features

Halogen free	yes
--------------	-----

Authorization/approvals

Approvals	UL 2238
-----------	---------

Classifications

eCl@ss 11.1	27-06-03-11
ETIM 9.0	EC002638

Declarations of conformity

RoHS Directive	2011/65/EU (EN 50581:2012)
----------------	----------------------------

Product description	M12 Male cable connector, Contacts: 8, shielded, moulded on the cable, IP67, UL 2238, PUR, black, 8 x 0.25 mm², 2 m
Area	M12-A
Coding	A-coded
Series	763
Part no.	77 3529 0000 50708-0200

General Disclaim Notice

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.

To protect against unintentional opening of the connector, the thread between the housing and the connector head must be secured with a suitable cyanoacrylate adhesive when used in circuits with voltages dangerous to the touch. This does not apply to connectors used in SELV and PELV circuits according to IEC 61140 (EN 61140, VDE 0140-1).

Connectors which are used in circuits with voltages dangerous to the touch may only be installed and used by, or under the supervision of, persons with electrical engineering training, taking into account the applicable regulations and standards.

The user must take suitable safety precautions to ensure that the connector cannot be accidentally disconnected.

Plug connectors with enclosure protection IP67 and IP68 are not suitable for use under water. When used outdoors, the plug connectors must be protected separately against corrosion. For further information on the IP protection classes, please refer to the "Technical Information" download centre.

Please observe the pollution degree and the overvoltage category. For further information, please refer to the download center "Technical Information".

To lock the cable connector with the device connector, the threaded ring is tightened "hand-tight" (approx. 60 cNm).

The protection class specification applies on condition that the four mounting holes are made as blind holes.