

TB62763FMG

Step Up Type DC/DC Converter for White LED


The TB62763FMG is a high efficient Step-Up Type DC/DC Converter specially designed for constant current driving of White LED.

This IC can drive 2-6 Hi-current type white LEDs connected series using a Li-ion battery.

This IC contains N-ch MOS-FET Transistor for Coil-Switching, and LED current (IF) is set with an external resistor.

This IC is especially for driving back light white LEDs in LCD of PDA, Cellular Phone, or Handy Terminal Equipment.

The TB6263FMG is RoHS.




Weight : 0.017 g (Typ.)


Features

- Variable LED current IF is set with a external resistor: 80mA (typ.)
- High current accuracy: +/- 1.5%
- High output power : 3W LED loading @(VOUT=20V、VIN=5V)
- High efficiency: 80% over (using recommended external parts)
- Output over voltage shutdown function
: Switching operation is shut down when OVP terminal voltage is over 32.5 V (typ.).
- Soft start function included
- Adjustable switching frequency (200kHz - 2MHz)
- Package : SON-P-0303-0.65

Pin Assignment (top view)




Week 1 to 26



Week 27 to 53

Note: This IC could be destroyed in some case if amounting in 180° inverse direction.
Please be careful about IC direction in mounting.

Block Diagram




Pin Function


Pin No.	Symbol	Function Description
1	SW	Switch terminal for DC/DC converter. Nch MOSFET built-In.
2	OVP	Over voltage protection terminal. IC switching operation is disabled with protection over voltage. If the voltage returns to recover level or less, operation is enabled again.
3	FB	LED I _F setting resistor connecting terminal.
4	SS	Setting the constant to limit the current when DC-DC operation starts. The rising time is changed depending on the constant of the capacitance. If capacitance is no connecting in this terminal, IC operate without soft-start function.
5	EN	Voltage-input terminal for IC-enable/disable LED-I _F . A high input on this pin enables the IC to operate while a low input causes it to shut down. The behavior of the IC is unpredictable if the input on the pin is undefined. Ensure that the pin is tied to either a high or low level.
6	VIN	Supply voltage input terminal. (2.8 V to 5.5 V)
7	FSET	Connect to resistance for internal frequency setup. (0.2~2MHz)
8	GND	Ground terminal.

I/O Equivalent Pin Circuits


1. SW




2. OVP




3. FB




4. SS




5. EN



6. VIN, GND



7. FSET



Absolute Maximum Ratings (Ta = 25°C if without notice)

Characteristics	Symbol	Rating	Unit
Power supply voltage	VIN	-0.3~ +6.0	V
Input voltage	VIN(EN)	-0.3~ +VIN + 0.3 (Note 1)	V
Switching terminal voltage	VO (SW)	-0.3~ +48	V
Power dissipation	PD	0.36 (device)	W
		0.64 (on PCB) (Note 2)	
Thermal resistance	Rth (j-a)	340 (device)	°C/W
		193 (on PCB)	
Operation temperature range	Topr	-40~+ 85	°C
Storage temperature range	Tstg	-55~+ 150	°C
Maximum junction temperature	Tj	150	°C

Note 1: Ensure that the supply voltage never exceeds 6.0 V.

Note 2: The power dissipation decreases the reciprocal of the saturated thermal resistance (1/ Rth(j-a)) for each degree (1°C) that the ambient temperature is exceeded (Ta = 25°C).

Note 3: PCB condition 40.0 x 40.0 x 1.6 mm, Cu 40%,FR-4

Recommended Operating Condition (Ta = -40 to 85°C if without notice)


Characteristics	Symbol	Tes Circuit	Test Condition	Min	Typ.	Max	Unit
Power supply voltage	VIN	—		2.8	—	5.5	V
LED current	IF	—	VIN = 5.0 V, RSENS = 6.26Ω 6 white LEDs, Ta = 25°C	—	80	—	mA

Electrical Characteristics (Ta = 25°C, VIN = 4.5 to 5.5 V if without notice)


Characteristics	Symbol	Test Circuit	Test Condition	Min	Typ.	Max	Unit
Power supply voltage	VIN	—		2.8	—	5.5	V
Operating consumption current	IIN (ON)	1	VEN= VIN, VFB=1V	—	0.6	0.9	mA
Quiescent consumption current	IIN (OFF)	2	VEN= 0 V	—	0.5	1.0	μA
EN terminal "H" level input voltage	VENH	3	—	1.3	—	VIN	V
EN terminal "L" level input voltage	VENL	3	—	0	—	0.4	V
EN terminal current	IEN	4	VEN=5.0 V or 0 V	—	0	1.0	μA
Integrated MOS-Tr switching frequency	fOSC	5	RFSET=47k	1.69	1.84	1.99	MHz
			RFSET=91k	0.92	1.00	1.08	MHz
			RFSET=470k	199	217	235	kHz
FSET terminal voltage	VFSET	6		—	1.2V	—	V
FSET terminal current	IFSET	7		11.8	13.2	14.6	μA
SS terminal voltage	VSS	8		880	960	1060	mV
SS terminal current	ISS	9		—	18	—	μA
SW terminal leakage current	Ioz (SW)	10	—	—	0.5	1	μA
FB terminal feedback voltage	VFB	11	RSNS = 6.25Ω	492.5	500.0	507.5	mV
		11	RSNS = 62.5Ω	492.5	500.0	507.5	mV
FB terminal line regulation	ΔVFB	11	VIN = 3.6 V standard VIN = 3.0~5.0 V VOU = 20V,ILED = 80mA	-2	—	2	%
FB terminal current	IFB	12	VEN= 5.0V, VFB = 500mV	—	0.02	—	μA
OVP terminal protection voltage	VOVP	13	—	30.0	32.5	35.0	V
OVP terminal recover voltage	VREC	13	—	29.0	31.5	34.0	V
OVP terminal hysteresis voltage	VOVPHYS	13	VOVPHYS= VOVP-VREC	0.5	1.0	2.0	V
OVD terminal leakage current	IOVP	14	VOVD = 28V	—	0.5	1	μA

Test Circuits


1. Operating consumption current




2. Quiescent consumption current




3. EN terminal "H" level and "L" level input voltage




4. EN terminal current




5. Integrated MOS-T_r switching frequency




6. FSET terminal voltage




7. FSET terminal current




8. SS terminal voltage




9. SS terminal current




10. SW terminal leakage current




11. FB terminal feedback voltage and FB terminal line regulation




12. FB terminal current



13. OVP terminal protection voltage, OVP terminal recover voltage OVP terminal hysteresis voltage



14. OVD terminal leakage current




Function diagram

The mode selecting shown below with logic input EN terminal.

EN	MODE
H	Operation mode
L	Shutdown mode

State Transition Diagram



	State	boost circuit	OVP circuit	OSC circuit	Internal reference circuit	Soft start circuit
	Shutdown	Stop	Stop	Stop	Stop	Stop
	EN: L to H	-	-	-	-	-
	Operation	Operate	Operate	Operate	Operate	Operate
	OVP detect	-	-	-	-	-
	OVP operation	Stop	Operate	Stop	Operate	Operate
	OVP release	-	-	-	-	-
	EN: H to L	-	-	-	-	-

Usage Precautions

Protection in LED Opened Condition

The operation with OVD terminal is available for the protection in case LED circuit opened.

When the voltage of OVD terminal is over 32.5 V (typ.), Nch MOS switching operation is disabled in the IC. When the voltage of OVD terminal drops below 31.5 V (typ.), Nch MOS switching operation becomes available again.

If load of LED is detached, Nch MOS switching operation is disabled with detection of boost circuit voltage and the IC is protected from unexpected over voltage.

Setting of Capacitor

The recommended values are

$$C_1 = 2.2 \text{ (}\mu\text{F)} \text{ or more, } C_2 = 1.0 \text{ (}\mu\text{F)} \text{ or more}$$

The capacitor of ceramic condenser tends to decrease when voltage is applied.

So, please select the appropriate capacitor in consideration of IC characteristics of withstand voltage and size.

Setting of I_F

Resistance connects between FB pin and GND.

The average current is set by this REXT value and average current are obtained by the following equation.

$$I_F \text{ (mA)} = \frac{500 \text{ [mV]}}{R_{EXT} \text{ [}\Omega\text{]}}$$

Current value error is within $\pm 1.5\%$. (Not included the REXT error)

Setting of External Inductor Size

Please select the inductor size with referring this table corresponding to each number of switching frequency.

[Recommended inductor values]

Switching frequency	Indictor Value	Note
200~500kHz	22 μH	LED current $I_F = 80 \text{ mA}$
Up to 500kHz	10 μH	

Setting of Switching frequency

Resistance connects between FSET pin and GND pin.

Switching frequency "fosc (kHz)" can be set by resistance value.


Switching frequency "fosc (kHz)" are obtained by the following equation.

$$F_{osc} \text{ (kHz)} = 66231 \times R_{FSET} \text{ (k}\Omega\text{)}^{-0.9299}$$


Setting error is within $\pm 8\%$. (Not included the Resistance error)

Application


1. normal application




2. No use the soft -start function



3. Input the PWM signal to adjust the Switching frequency and LED current




4. 2 lines control



Package Dimensions

SON8-P-0303-0.65

Unit: mm



weight : 0.017 g (Typ.)

• Notes on Contents**1. Block Diagrams**

Some of the functional blocks, circuits, or constants in the block diagram may be omitted or simplified for explanatory purposes.

2. Equivalent Circuits

The equivalent circuit diagrams may be simplified or some parts of them may be omitted for explanatory purposes.

3. Timing Charts

Timing charts may be simplified for explanatory purposes.

4. Application Circuits

The application circuits shown in this document are provided for reference purposes only. Thorough evaluation is required, especially at the mass production design stage.

Toshiba does not grant any license to any industrial property rights by providing these examples of application circuits.

5. Test Circuits

Components in the test circuits are used only to obtain and confirm the device characteristics. These components and circuits are not guaranteed to prevent malfunction or failure from occurring in the application equipment.

IC Usage Considerations**Notes on handling of ICs**

- [1] The absolute maximum ratings of a semiconductor device are a set of ratings that must not be exceeded, even for a moment. Do not exceed any of these ratings.
Exceeding the rating(s) may cause the device breakdown, damage or deterioration, and may result injury by explosion or combustion.
- [2] Use an appropriate power supply fuse to ensure that a large current does not continuously flow in case of over current and/or IC failure. The IC will fully break down when used under conditions that exceed its absolute maximum ratings, when the wiring is routed improperly or when an abnormal pulse noise occurs from the wiring or load, causing a large current to continuously flow and the breakdown can lead smoke or ignition. To minimize the effects of the flow of a large current in case of breakdown, appropriate settings, such as fuse capacity, fusing time and insertion circuit location, are required.
- [3] If your design includes an inductive load such as a motor coil, incorporate a protection circuit into the design to prevent device malfunction or breakdown caused by the current resulting from the inrush current at power ON or the negative current resulting from the back electromotive force at power OFF. IC breakdown may cause injury, smoke or ignition. Use a stable power supply with ICs with built-in protection functions. If the power supply is unstable, the protection function may not operate, causing IC breakdown. IC breakdown may cause injury, smoke or ignition.
- [4] Do not insert devices in the wrong orientation or incorrectly.
Make sure that the positive and negative terminals of power supplies are connected properly.
Otherwise, the current or power consumption may exceed the absolute maximum rating, and exceeding the rating(s) may cause the device breakdown, damage or deterioration, and may result injury by explosion or combustion.
In addition, do not use any device that is applied the current with inserting in the wrong orientation or incorrectly even just one time.

Points to remember on handling of ICs

(1) Over current Protection Circuit

Over current protection circuits (referred to as current limiter circuits) do not necessarily protect ICs under all circumstances. If the Over current protection circuits operate against the over current, clear the over current status immediately.

Depending on the method of use and usage conditions, such as exceeding absolute maximum ratings can cause the over current protection circuit to not operate properly or IC breakdown before operation. In addition, depending on the method of use and usage conditions, if over current continues to flow for a long time after operation, the IC may generate heat resulting in breakdown.

(2) Thermal Shutdown Circuit

Thermal shutdown circuits do not necessarily protect ICs under all circumstances. If the thermal shutdown circuits operate against the over temperature, clear the heat generation status immediately.

Depending on the method of use and usage conditions, such as exceeding absolute maximum ratings can cause the thermal shutdown circuit to not operate properly or IC breakdown before operation.

(3) Heat Radiation Design

In using an IC with large current flow such as power amp, regulator or driver, please design the device so that heat is appropriately radiated, not to exceed the specified junction temperature (T_J) at any time and condition. These ICs generate heat even during normal use. An inadequate IC heat radiation design can lead to decrease in IC life, deterioration of IC characteristics or IC breakdown. In addition, please design the device taking into consideration the effect of IC heat radiation with peripheral components.

(4) Back-EMF

When a motor rotates in the reverse direction, stops or slows down abruptly, a current flow back to the motor's power supply due to the effect of back-EMF. If the current sink capability of the power supply is small, the device's motor power supply and output terminals might be exposed to conditions beyond maximum ratings. To avoid this problem, take the effect of back-EMF into consideration in system design.

The following conditions apply to solderability:

About solderability, following conditions were confirmed

- Solderability

- (1) Use of Sn-37Pb solder Bath

- solder bath temperature: 230
- dipping time: 5 seconds
- the number of times: once
- use of R-type flux

- (2) Use of Sn-3.0Ag-0.5Cu solder Bath

- solder bath temperature: 245
- dipping time: 5 seconds
- the number of times: once
- use of R-type flux

RESTRICTIONS ON PRODUCT USE

- Toshiba Corporation, and its subsidiaries and affiliates (collectively "TOSHIBA"), reserve the right to make changes to the information in this document, and related hardware, software and systems (collectively "Product") without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before creating and producing designs and using, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application that Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications. **TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.**
- Product is intended for use in general electronics applications (e.g., computers, personal equipment, office equipment, measuring equipment, industrial robots and home electronics appliances) or for specific applications as expressly stated in this document. Product is neither intended nor warranted for use in equipment or systems that require extraordinarily high levels of quality and/or reliability and/or a malfunction or failure of which may cause loss of human life, bodily injury, serious property damage or serious public impact ("Unintended Use"). Unintended Use includes, without limitation, equipment used in nuclear facilities, equipment used in the aerospace industry, medical equipment, equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or explosions, safety devices, elevators and escalators, devices related to electric power, and equipment used in finance-related fields. Do not use Product for Unintended Use unless specifically permitted in this document.
- Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- **ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE FOR PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (2) DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO SALE, USE OF PRODUCT, OR INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.**
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). Product and related software and technology may be controlled under the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product. Please use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. TOSHIBA assumes no liability for damages or losses occurring as a result of noncompliance with applicable laws and regulations.