

CUC-DSC-J1BAU-S/DSC28 - D-SUB crimp contact



1418787

<https://www.phoenixcontact.com/gb/products/1418787>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



D-SUB crimp contact, connection method: Crimp connection, connection cross section: AWG 28-24

Product description

Standard contact for D-SUB contact inserts

Your advantages

- High grade
- Various connection methods for every application
- Turned contact

Commercial data

Item number	1418787
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	ABNCAC
Product key	ABNCAC
Catalog page	Page 446 (C-2-2019)
GTIN	4055626150741
Weight per piece (including packing)	0.265 g
Weight per piece (excluding packing)	0.23 g
Customs tariff number	85366990
Country of origin	CH

CUC-DSC-J1BAU-S/DSC28 - D-SUB crimp contact



1418787

<https://www.phoenixcontact.com/gb/products/1418787>

Technical data

Mounting

Mounting type	Crimp connection
---------------	------------------

Product properties

Product type	Crimp contact
Series	HC-M-DSUB-C
	HC-M-08-GBIT
	HC-M-25
	HC-M-EMV
Type	Individual female contact
Contact material type	turned

Connection data

Connection method	Crimp connection
Contact connection type	Socket
Connection technology	Crimp connection
Conductor cross section	0.08 mm² ... 0.12 mm²
Connection cross section AWG	28 ... 24

Material specifications

Material	Metal
Contact material	Copper alloy
Contact surface material	0.2 µm, gold over nickel

Dimensions

Width	1.74 mm
Height	1.74 mm
Length	13.6 mm

Mechanical characteristics

Contact diameter	1 mm
------------------	------

Electrical properties

Maximum load current	5 A
Rated surge voltage	1.2 kV
	1.2 kV (1 min.)
Rated current	5 A (at 20 °C)

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 200
Insertion force per signal contact	≤ 3.40 N

CUC-DSC-J1BAU-S/DSC28 - D-SUB crimp contact



1418787

<https://www.phoenixcontact.com/gb/products/1418787>

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-55 °C ... 130 °C
---------------------------------	-------------------

CUC-DSC-J1BAU-S/DSC28 - D-SUB crimp contact



1418787

<https://www.phoenixcontact.com/gb/products/1418787>

Classifications

ECLASS

ECLASS-13.0	27440392
-------------	----------

ETIM

ETIM 9.0	EC002943
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

1418787

<https://www.phoenixcontact.com/gb/products/1418787>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	f52bacdb-a359-4b42-a3d0-32d0f22a71ac

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk