



Brand of NTN corporation

Technical data

UCT322 Bearing units




Grey cast housing, radial insert ball bearing with socket set screws, seal with slinger

KIT CONTENT

UC322G2, T322

VISUAL (S)



PRODUCT DEFINITION

Brand	SNR
A - Housing width	130 mm
A1 - Width of location slot	38 mm
A2	80 mm
B - Width of Inner Ring	117 mm
d - Shaft diameter	110 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION	
G - Grease fitting	M10x1
H - Housing length, width or diameter	320 mm
H1 - Distance between location slots	285 mm
H2 - Housing height / width	185 mm
L - Housing length	385 mm
L1 - Distance attachment end face to bearing centerline	235 mm
L2 - Thickness of attachment end	40 mm
L3 - Length of guidance slot/face	215 mm
N - Mounting hole dimension	65 mm
N1 - Length of attachment slot	52 mm
N2 - Height of attachment slot	125 mm
S - Distance front side/bearing centre	46 mm

PRODUCT PERFORMANCE	
C - Dynamic load rating	205000000 mN
C0 - Static load rating	178000000 mN
Operating temperature min.	253,15 °K
Operating temperature max.	373,15 °K

OTHER FEATURES	
Mass	38,6 kg
Recommended tightening torque for set screw	75 N-m

