



SIMATIC ET 200SP, PROFINET interface module IM 155-6 PN Basic, max. 16 I/O modules, 2x integrated RJ45 sockets PN security class 1 including server module (6ES7193-6PA00-0AA0)

General information	
Product type designation	IM 155-6 PN BA
Firmware version	V6.3
<ul style="list-style-type: none"> FW update possible 	Yes
Vendor identification (VendorID)	0x002A
Device identifier (DeviceID)	0x0313
Product function	
<ul style="list-style-type: none"> I&M data 	Yes; I&M0 to I&M4
<ul style="list-style-type: none"> Module swapping during operation (hot swapping) 	Yes; Multi-hot swapping
<ul style="list-style-type: none"> Isochronous mode 	No
<ul style="list-style-type: none"> IRT 	No
Engineering with	
<ul style="list-style-type: none"> STEP 7 TIA Portal configurable/integrated from version 	V19
<ul style="list-style-type: none"> STEP 7 configurable/integrated from version 	V5.7 SP3
<ul style="list-style-type: none"> PROFINET from GSD version/GSD revision 	GSDML V2.43
Configuration control	
via dataset	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Short-circuit protection	Yes
Mains buffering	
<ul style="list-style-type: none"> Mains/voltage failure stored energy time 	5 ms
Input current	
Current consumption (rated value)	200 mA
Current consumption, max.	300 mA
Inrush current, max.	1 A
I ² t	0.05 A ² ·s
Power loss	
Power loss, typ.	1.8 W
Address area	
Address space per module	
<ul style="list-style-type: none"> Address space per module, max. 	128 byte; For input and output data respectively
Address space per station	
<ul style="list-style-type: none"> Address space per station, max. 	128 byte
Hardware configuration	
Rack	
<ul style="list-style-type: none"> Quantity of operable ET 200SP modules, max. 	16

• Quantity of operable ET 200AL modules, max.	0
Interfaces	
Number of PROFINET interfaces	1; 2 ports (switch)
1. Interface	
Interface types	
• RJ 45 (Ethernet)	Yes; 2 integrated RJ45 ports
• Number of ports	2; integrated RJ45 ports
• integrated switch	Yes
• BusAdapter (PROFINET)	No
Protocols	
• PROFINET IO Device	Yes
• Open IE communication	Yes
• Media redundancy	Yes; PROFINET MRP client
PROFINET IO Device	
Services	
— IRT	No
— PROFinergy	Yes
— Prioritized startup	No
— Shared device	No
Interface types	
RJ 45 (Ethernet)	
• Transmission procedure	PROFINET with 100 Mbit/s full duplex (100BASE-TX)
• 100 Mbps	Yes
• Autonegotiation	Yes
• Autocrossing	Yes
Protocols	
Supports protocol for PROFINET IO	Yes
PROFIsafe	No
PROFIBUS	No
EtherNet/IP	No
Modbus TCP	No
Redundancy mode	
• PROFINET system redundancy (S2)	No
Media redundancy	
— MRP	Yes
— MRPD	No
Open IE communication	
• TCP/IP	Yes
• SNMP	Yes
• LLDP	Yes
Interrupts/diagnostics/status information	
Status indicator	Yes
Alarms	Yes
Diagnostics function	Yes
Diagnostics indication LED	
• RUN LED	Yes; green LED
• ERROR LED	Yes; red LED
• MAINT LED	Yes; Yellow LED
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Connection display LINK TX/RX	Yes; 2x green LED
Potential separation	
between backplane bus and electronics	No
between PROFINET and all other circuits	Yes; 1500 V AC (type test)
between supply and all other circuits	No
Permissible potential difference	
between different circuits	Safety extra low voltage SELV
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
Network loading class	3

product functions / security / header

PROFINET Security Class	1
signed firmware update	Yes
Secure Boot	No
safely removing data	Yes
data integrity	Yes

Ambient conditions

Ambient temperature during operation	
• horizontal installation, min.	-30 °C; No condensation
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C; No condensation
• vertical installation, max.	50 °C

Altitude during operation relating to sea level

• Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual
---	--

connection method

ET-Connection

• via BU/BA Send	No
------------------	----

Mechanics/material

Strain relief	No
---------------	----

Dimensions

Width	35 mm
Height	117 mm
Depth	74 mm

Weights

Weight, approx.	125 g
-----------------	-------

Classifications

	Version	Classification
eClass	14	27-24-26-08
eClass	12	27-24-26-08
eClass	9.1	27-24-26-08
eClass	9	27-24-26-08
eClass	8	27-24-26-08
eClass	7.1	27-24-26-08
eClass	6	27-24-26-08
ETIM	9	EC001604
ETIM	8	EC001604
ETIM	7	EC001604

Approvals / Certificates

General Product Approval



[Manufacturer Declaration](#)

[Miscellaneous](#)

[KC](#)

[PROFINET](#)

General Product Approval **EMV** **For use in hazardous locations**



[KC](#)



[CCC-Ex](#)

[FM](#)

For use in hazardous locations **Maritime application**



ATEX



IECEX

[Miscellaneous](#)



ABS



BUREAU
VERITAS



DNV

Maritime application



LRS

[NK / Nippon Kaiji Ky-
okai](#)



RINA



RMRS

[CCS \(China Classifica-
tion Society\)](#)



KR
KOREAN REGISTER

last modified:

4/10/2025