

Datasheet

RS Pro FDNYD2 series Blue Insulated Crimp Receptacle, 4.75 x 0.5mm, 1.5mm² to 2.5mm², 16AWG to 14AWG, Copper Plated

RS Stock No: **267-4237**



Product Details

RS Pro insulated crimp receptacle in yellow colour, has 4.75 x 0.5 mm tab size and 1.5 mm² to 2.5 mm², 16 AWG to 14 AWG wire size with copper plating. It has a range of insulated double crimp receptacle wire terminal made from brass with a copper sleeved barrel. This female wire connector is nylon or vinyl insulation with a flared design for easy wire insertion. The insulation of these female crimp connectors is colour coded to correspond with the wire size they are used with.

Features and Benefits

- Insulated double crimp receptacle wire terminals made from brass with a copper sleeved barrel
- Female wire connectors have nylon or vinyl insulation with a flared design for easy wire insertion
- Insulation of these female crimp connectors is colour coded to correspond with the wire size

Specifications:

Colour	Blue
Connector Type	Quick Disconnect Terminal
Contact Material	Brass
Contact Plating	Copper
Gender	Female
Insulation	Insulated
Insulation Material	Nylon
Length	20 mm
Maximum Wire Size (AWG)	14 AWG
Maximum Wire Size (mm ²)	2.5 mm ²
Minimum Wire Size (AWG)	16 AWG
Minimum Wire Size (mm ²)	1.5 mm ²
Tab Size	4.75 x 0.5 mm
Wire Size	16 to 14 AWG
Current Rating	10 to 15 A
Temperature Rating	+105°C
Type	Double Crimp
Voltage Rating	600 V
Width	5 mm