

Eaton 186179

Catalog Number: 186179

Eaton Moeller® series C22 Changeover switch, With thumb-grip, maintained, 2 NC, Cable (black) with non-terminated end, 4 pole, 3.5 m, 2 positions, Bezel: titanium

General specifications



Product Name

Eaton Moeller® series C22 Changeover switch

Catalog Number

186179

EAN

4015081816804

Product Length/Depth

3576 mm

Product Height

30 mm

Product Width

30 mm

Product Weight

0.122 kg

Certifications

VDE 0660
CE
CSA
IEC/EN 60947-5-1
UL
CSA File No.: 165628
CSA Class No.: 321103
UL File No.: E29184
UL 508
CSA-C22.2 No. 14-18 and No. 94.2-15
CE marking
UL Category Control No.: NKCR
UL listed, CSA certified

Catalog Notes

Contacts with safety function, by positive opening to IEC/EN 60947-5-1

Product specifications

Type

Selector switch actuator

Actuator color

Black

Product Category

RMQ compact solution

Actuator function

Maintained

Switching function latching

Electric connection type

Other

Fitted with:

Front ring

Operating frequency

2000 Operations/h

Pollution degree

3

Climatic proofing

Damp heat, constant, to IEC 60068-2-78

Damp heat, cyclic, to IEC 60068-2-30

Connection to SmartWire-DT

No

Rated impulse withstand voltage (Uimp)

800 V AC

Actuator type

Toggle

Actuator diameter

4.7 mm

Actuator travel and actuation force (DIN EN 60947-5-1)

4.65 mm

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-30 °C

Force for positive opening - min

30 N

Resources

Catalogs

[eaton-pushbuttons-signal-towers-sensors-assortment-overview-catalog-ca047003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-00004135.pdf](#)

[DA-DC-00004157.pdf](#)

Drawings

[eaton-operating-c22-changeover-switch-dimensions.eps](#)

[eaton-operating-c22-changeover-switch-3d-drawing.eps](#)

eCAD model

[DA-CE-ETN.C22-WRK-K02-P65](#)

Installation instructions

[IL047016ZU](#)

Installation videos

[Eaton's RMQ compact solution pilot devices](#)

mCAD model

[DA-CD-c22_w_open_cable](#)

[DA-CS-c22_w_open_cable](#)

Sales notes

[eaton-rmq-mci-multi-color-light-indicator-flyer-fl047005en-en-us.pdf](#)

System overview

[Pilot devices - selection aid](#)

Wiring diagrams

[eaton-operating-c22-pushbutton-wiring-diagram-004.eps](#)

Knob travel

5.7 mm

Number of contacts (change-over contacts)

0

Number of contacts (normally closed contacts)

2

Number of contacts (normally open contacts)

0

Opening diameter

22.5 mm

Opening height

0 mm

Operating torque

0.3 Nm

Rated insulation voltage (Ui)

250 V

Rated operational current (Ie) at AC-15, 24 V

4 A

Rated operational current (Ie) at DC-13, 24 V

3 A

Bezel color

Titanium

Cable material

PUR

Bezel material

Plastic

Design

With thumb-grip

Cable end open

Classical

Mounting position

As required

Rated conditional short-circuit current (Iq)

1 kA

Cable length

3.5 m

Connection type

Cable (black) with non-terminated end, 4 pole

Overvoltage category

III

Control circuit reliability

1 failure per 900,000 switching operations statistically determined, at 17 V DC/7 mA: N/C contact)

Degree of protection

IP65, rear

IP66

NEMA Other

Shock resistance

30 g, Mechanical, Shock duration 11 ms

Number of switch positions

2

Tightening torque

2 Nm, Threaded ring

Short-circuit protection rating

Max. 4 A gG/gL, Fuse, Contacts

Supply voltage - max

0 V

Supply voltage - min

0 V

Switching angle

60 °

Width opening

0 mm