




Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Holder**

Primary Product Color: **Natural**

Number of Positions: **26**

Operating Temperature (Max): **105 °C [221 °F]**

Operating Temperature Range: **-30 – 105 °C [-22 – 221 °F]**

Features

Product Type Features

Connector Hardware Accessory Type	Holder
Hardware Accessory Function	Mounting

Configuration Features

Number of Positions	26
---------------------	----

Body Features

Primary Product Color	Natural
-----------------------	---------

Housing Features

Centerline (Pitch)	1.5 mm[.059 in]
--------------------	-----------------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

--	--



Packaging Method	Package
Packaging Quantity	500

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-353908-3
CT REC HSG 13P CRIMP TYPE WHIT



TE Part # 2-292262-6
DBL ROW (H) DIP TYPE WITH BOAR




TE Part # 2-292208-6
MINI CT D/R DIP 26P V NAT




TE Part # CAT-AM7053-C7671
Mini Common Termination Contacts




TE Part # 2-292229-6
1.5 MINI CT D/R SMT 26P V ONTA



TE Part # 1-353293-3
MINI CT MT REC ASSY 13P GRAY



TE Part # 2-292216-6
MINI CT D/R RELAY 26P V NAT



TE Part # 7-292216-6
MINI CT D/R RELAY 26P V BLUE


Also in the Series | AMP Mini CT



Connector Contacts(4)



Connector Hardware(10)



PCB Headers & Receptacles(332)




Wire-to-Board Connector Assemblies & Housings(172)



Wire-to-Board Headers & Receptacles (332)

Customers Also Bought



TE Part #1-353293-2
MINI CT MT REC ASSY 12P GRAY



TE Part #292156-2
CT RELAY HDR ASSY FREE HANGING




TE Part #2-1674755-0
REC ASSY FOR MINI CT HYBIRD DR




TE Part #3-353294-0
AMP MINI D/R HDR HSG 30P NATU



TE Part #3-353294-4
AMP MINI D/R HDR HSG 34P NATU



TE Part #4-292216-0
MINI CT D/R RELAY 40P V NAT



TE Part #3-292246-4
1.5 MINI CT LATTICE REC KEY B



TE Part #2-292215-4
MINI CT SGL RELAY 4P BLACK



Documents

Product Drawings

AMP MINI D/R HDR HSG 26P NATU

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_2-353294-6_E.3d_igs.zip

English

Customer View Model

ENG_CVM_2-353294-6_E.3d_stp.zip

English

Customer View Model

ENG_CVM_2-353294-6_E.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English