



Relays & Contactors > Electromechanical Relays



Relay & Contactor Type: **Time Delay Relay**
Current Type: **DC**
Contact Arrangement: **2 Form C DPDT-CO**
Contact Current Rating: **10 A**
Environmental Ambient Temperature (Max): **75 °C [167 °F]**

Features

Product Type Features

Relay & Contactor Type	Time Delay Relay
------------------------	------------------

Configuration Features

Relay Options	Tamper-Proof Cap
Contact Arrangement	2 Form C DPDT-CO

Electrical Characteristics

Input Voltage	28 VDC
Contact Current Rating	10 A

Usage Conditions

Operating Temperature Range	-30 – 75 °C
Environmental Ambient Temperature (Max)	75 °C[167 °F]

Operation/Application

Type of Control	Knob
Timing Range (Off-Time)	60 – 600 seconds
Mode of Operation	Off-Delay
Repeatability (Max)	±10%
Current Type	DC

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series | Agastat 7000

AC Relays(8)

DC Relays(33)

Electromechanical Relays(41)

Customers Also Bought





TE Part #6-1472995-2

7012OBILM=RLY,STD,ON,2P,24V,5S,I,
L,M



TE Part #342117-1

22-16 F.E.P.G. SPADE 4BA STUD




TE Part #EC0437-000

06153411



TE Part #1-2176398-4

3502 47K 1%



TE Part #165565-6

TERM,RECPT,PIDG,110 FAST, 22-16,
PHBR,AU



TE Part #2176398-2

3502 15K 1%



TE Part #9-2176397-8

3502 11K 1%



TE Part #3-1755142-2

7022MEIM=RLY,STD,OFF,2P,28V,200S,
I,M



TE Part #3-1755142-3

7022WKT=RLY,STD,OFF,2P,96V,300S,T



TE Part #342066

16-14 H.D.R/T 1/2" STUD BLACK

Documents

Product Drawings

7022MFI=RLY,STD,2P,OFF,28V,10M,I

English

Datasheets & Catalog Pages

5-1773450-5_sec12_7000

English