

Fair-Rite Products Corp. Your Signal Solution_®

Fair-Rite Product's Catalog Part Data Sheet, 5943002701 Printed: 2013-07-03



Ferrite Components for the Electronics Industry Fair-Rite Products Corp. PO Box J,One Commercial Row, Wallkill, NY 12589-0288 Phone: (888) 324-7748 www.fair-rite.com







Part Number:	5943002701
Frequency Range:	Low-Medium Permeability, 43 (ui=800) material
Description:	43 TOROID
Application:	Inductive Components
Where Used:	Closed Magnetic Circuit
Part Type:	Toroids

Mechanical Specifications

Weight: 33.000 (g)

Part Type Information

A ring configuration provides the ultimate utilization of the intrinsic ferrite material properties. Toroidal cores are used in a wide variety of applications such as power input filters, ground-fault interrupters, common-mode filters and in pulse and broadband transformers.

-Toroids are listed by initial permeability classes and increasing dimension of the inside diameter.

-All toroidal cores are supplied burnished to break sharp edges.

-Toroids are tested for AL values at 10 kHz.

-Toroids with an outside diameter of 9.5mm (.375") or smaller can be supplied Parylene C coated. The Parylene coating will increase the 'A' and 'C' dimensions and decrease the 'B' dimension a maximum of 0.038mm (.0015"). The ninth digit of a Parylene coated toroid part number is a '1'. See the material characteristics of Parylene C in our online catalog.

-Toroids with an outside diameter of 9.5mm (.375") or larger can be supplied with a uniform coating of thermo-set plastic coating. This coating will increase the 'A' and 'C' dimensions and decrease the 'B' dimension a maximum of 0.5mm (.020"). The 9th digit of the thermo-set plastic coated toroid part number is a '2'. Thermo-set plastic coating is RoHS compliant.

-Thermo-set plastic coated parts can withstand a minimum breakdown voltage of 1000 Vrms, uniformly applied across the 'C' dimension of the toroid.

-The "C" dimension may be modified to suit specific applications.

-For any toroidal core requirement not listed in the catalog, please contact our customer service department for availability and pricing.

-Explaination of Part Numbers: Digits 1&2 = product class, 3&4 = material grade, 9th digit 1 = Parylene coating, 2 = thermo-set plastic coating.

Fair-Rite Products Corp. Your Signal Solution_®

Ferrite Components for the Electronics Industry

Fair-Rite Products Corp. PO Box J.One Commercial Row, Wallkill, NY 12589-0288 Phone: (888) 324-7748 www.fair-rite.com

Fair-Rite Product's Catalog Part Data Sheet, 5943002701 Printed: 2013-07-03



Mechanical Specifications

Dim	mm	mm	nominal	inch
		tol	inch	misc.
А	35.55	±0.75	1.400	-
В	23.00	±0.55	0.900	-
С	12.70	±0.50	0.500	-
D	-	-	-	-
E	-	-	-	-
F	-	-	-	-
G	-	-	-	-
Н	-	-	-	-
J	-	-	-	-
К	-	-	-	-

Electrical Specifications

Typical Impedance (Ω)		
Electrical Properties		
A _L (nH)	885 ±20%	
Ae(cm ²)	0.79000	
ΣI/A(cm ⁻¹)	11.20	
l _e (cm)	8.90	
V _e (cm ³)	7.00000	

Land Patterns

V	W	Х	Y	Z
	ref			
-	-	-	-	-
-	-	-	-	-

Winding Information

Turns	Wire	1st Wire	2nd Wire
Tested	Size	Length	Length
-	-	-	-

Reel Information

Tape Width	Pitch	Parts 7 "	Parts 13 "	Parts 14 "
mm	mm	Reel	Reel	Reel
-	-	-	-	-

Package Size

Pkg Size
-
(-)

Connector Plate

# Holes	# Rows
-	-

Legend

+ Test frequency

Preferred parts, the suggested choice for new designs, have shorter lead times and are more readily available.

The column H(Oe) gives for each bead the calculated dc bias field in oersted for 1 turn and 1 ampere direct current. The actual dc H field in the application is this value of H times the actual NI (ampere-turn) product. For the effect of the dc bias on the impedance of the bead material, see figures 18-23 in the application note How to choose Ferrite Components for EMI Suppression.

A ½ turn is defined as a single pass through a hole.

I/A - Core Constant

A_e: Effective Cross-Sectional Area

 A_{I} - Inductance Factor $\left(\frac{L}{N^{2}}\right)$

N/AWG - Number of Turns/Wire Size for Test Coil

I e: Effective Path Length

V_e: Effective Core Volume

NI - Value of dc Ampere-turns



Fair-Rite Product's Catalog Part Data Sheet, 5943002701 Printed: 2013-07-03



Ferrite Material Constants

Specific Heat	0.25 cal/g/ºC
Thermal Conductivity	3.5 - 4.5 mW/cm - °C
Coefficient of Linear Expansion	8 - 10x10 ⁻⁶ /ºC
Tensile Strength	4.9 kgf/mm ²
Compressive Strength	42 kgf/mm ²
Young's Modulus	15x10 ³ kgf/mm ²
Hardness (Knoop)	650
Specific Gravity	\approx 4.7 g/cm ³
The above quoted properties are typical for Fair-Rit	e MnZn and NiZn ferrites.

See next page for further material specifications.

Frite Products Corp. Your Signal Solution ® Ferrite Components for the Electronics Industry

Fair-Rite Products Corp. PO Box J,One Commercial Row, Wallkill, NY 12589-0288 Phone: (888) 324-7748 www.fair-rite.com

This NiZn is our most popular ferrite for suppression of conducted EMI from 20 MHz to 250 MHz. This material is also used for inductive applications such as high frequency common-mode chokes.

EMI suppression beads, beads on leads, SM beads, multi-aperture cores, round cable EMI suppression cores, round cable snap-its, flat cable EMI suppression cores, flat cable snap-its, miscellaneous suppression cores, bobbins, and toroids are all available in 43 material.


Fair-Rite Product's Catalog Part Data Sheet, 5943002701 Printed: 2013-07-03



43 Material Characteristics:


Property	Unit	Symbol	Value
Initial Permeability @ B < 10 gauss		μ	800
Flux Density	gauss	В	2900
@ Field Strength	oersted	н	10
Residual Flux Density	gauss	B,	1300
Coercive Force	oersted	He	0.45
Loss Factor	10-6	tan δ/μ _i	250
@ Frequency	MHz		1.0
Temperature Coefficient of Initial Permeability (20 -70°C)	%/°C		1.25
Curie Temperature	°C	Tc	>130
Resistivity	Ωcm	ρ	1x10 ⁵

Percent of Original Impedance vs. Temperature




Measured on a 2643000301 using the HP4291A.

Hysteresis Loop




Complex Permeability vs. Frequency



Measured on a 17/10/6mm toroid using the HP 4284A and the HP 4291A.





Measured on a 17/10/6mm toroid at 100kHz.

Measured on a 17/10/6mm toroid at 10kHz.