


4800S Series

Shielded Surface Mount Power Inductors



220

330

470

680

1000

48221SC

48331SC

48471SC

48681SC

48102SC

MECHANICAL DIMENSIONS	
12.20±0.30 (0.480±0.012) 48XXXSC XYYWW 12.20±0.30 (0.480±0.012)	7.60±0.5 (0.299±0.02)
6.00 (0.236) Max. Dot signifies the innermost turn of the winding.	Recommended Footprint Details
Dot signifies the innermost turn of the winding. All dimensions in mm (inches). Package weight: 3.1g Typ.	12.80 (0.504)

1.00

0.85

0.76

0.66

0.52

430

630

900

1250

1850

5

5

4

4

23

22

20

18

17

8.0

8.0

8.0

0.8

0.8

SOLDERING INFORMATION ²		
Storage temperature range	-40°C to 125°C	
Operating free air temperature range	-40°C to 85°C	



Specifications typical at $T_{\Delta} = 25^{\circ}C$

ABSOLUTE MAXIMUM RATINGS


- 1 Maximum DC current occurs when either the inductance falls to 75% of its nominal value or when its temperature rise reaches 40°C,
- 2 For further information, please visit www.murata-ps.com/rohs

Murata Power Solutions

- Integral EMI shield
- Compact size
- Tape and reel packaging
- UL 94V-0 materials
- J-STD-020-C reflow

DESCRIPTION


The 4800S series is a range of bobbin-wound, surface-mount inductors designed for use in switching power supply, and power line filter circuits. The parts are suitable for any application requiring a high saturation current in a low-profile package. The devices have an integral ferrite shield to reduce EMI.










Shielded Surface Mount Power Inductors







Shielded Surface Mount Power Inductors



This product is subject to the following operating requirements and the Life and Safety Critical Application Sales Policy:

Refer to: http://www.murata-ps.com/requirements/

Murata Power Solutions, Inc. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice.