

Cutter LXT®

DCC501

18V • 125 mm • 8 800 min⁻¹

BL motor provides high power and excellent cutting performance.

LXT® powered cutter with BL motor provides high power and excellent cutting performance. Water supply attachment with a tank capacity of 500 ml is supplied as standard equipment. Compatible with optional guide rail for increased maneuverability.



LXT **BL** **ADT** **AWS** **BRAKE**

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	8800 min ⁻¹
Max. Cutting Depth at 45°	27 mm
Bore Size (Arbor Diameter)	20 mm
AWS ready	✓
Sound Power Level (L _{WA})	107 dB(A)
Sound Pressure Level (L _{pA})	96 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Product net weight	2,4 kg
Tool weight with battery	2,7 - 3,0 kg
Product Dimensions (L x W x H):	283 x 163 x 172 mm
Brushless Motor	✓

User benefits

- Brushless motor provides high power and excellent cutting performance
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Two-stage safety trigger switch minimises accidental start up
- Large top handle design for increased comfort
- Wide blade case enables use of curved diamond wheel
- Battery protection system automatically shuts off power when the battery level is low
- Powerful cutting in stone, masonry, tile & concrete

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing