

BS-MAGAZINE EXT SET - Adapter set



1640724

<https://www.phoenixcontact.com/in/products/1640724>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Extension set for the feed magazines for use with high components.



Commercial data

Item number	1640724
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BH2XX1
GTIN	4067923167209
Weight per piece (including packing)	27.1 g
Weight per piece (excluding packing)	22 g
Country of origin	DE

BS-MAGAZINE EXT SET - Adapter set



1640724

<https://www.phoenixcontact.com/in/products/1640724>

Technical data

Dimensions

Width	45 mm
Height	90 mm
Length	45 mm

Material specifications

Color	transparent
Material	ABS, PC, PVC

Environmental and real-life conditions

Ambient conditions

Optimum ambient temperature (storage/transport)	20.00 °C 60.00 %
Ambient temperature (operation)	5 °C ... 35 °C
Ambient temperature (storage/transport)	0 °C ... 60 °C
Permissible humidity (operation)	10 % ... 80 %
Permissible humidity (storage/transport)	20 % ... 80 %

Mounting

Assembly note	Installation angle: 0° ... 10°
---------------	--------------------------------

BS-MAGAZINE EXT SET - Adapter set



1640724

<https://www.phoenixcontact.com/in/products/1640724>

Classifications

ECLASS

ECLASS-13.0	21100612
-------------	----------

ETIM

ETIM 9.0	EC011819
----------	----------

BS-MAGAZINE EXT SET - Adapter set



1640724
<https://www.phoenixcontact.com/in/products/1640724>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in