



 PRODUCT-DETAILS

OT1000E03W4P

OT1000E03W4P SWITCH-DISCONNECTOR



General Information

Extended Product Type	OT1000E03W4P
Product ID	1SCA022871R7310
EAN	6417019338569
Catalog Description	OT1000E03W4P SWITCH-DISCONNECTOR
Long Description	3-pole, front operated, base mounted switch-d disconnecter with black IP65 handle and shaft, wide phase distance. terminal bolt kit included

ABB EcoSolutions

End Of Life Disassembling Instructions	1SCC301120M0201
Environmental Information	1SCC301233D0201
Environmental Product Declaration - EPD	1SCC301300D0201

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
---	-----------------

REACH Declaration	1SCC011021D0201
RoHS Declaration	1SCC011020D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC011025D0201

Popular Downloads

Data Sheet, Technical Information	1SCC301020C0201
Instructions and Manuals	1SCC301047M0213
Mechanical Drawings	1SCC301909F0001 1SCC301908F0001 OT1250E03W4.igs
Environmental Product Declaration - EPD	1SCC301300D0201

Environmental

Degree of Protection	Front IP00
Environmental Information	1SCC301233D0201
Pollution Degree	3

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85365080
Country or Territory of Origin	Finland

Dimensions

Product Net Width	454.5 mm
Product Net Height	306 mm
Product Net Depth / Length	167 mm
Product Net Weight	17.8 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	400 mm
Package Level 1 Depth / Length	613 mm
Package Level 1 Height	170 mm
Package Level 1 Gross Weight	19.6 kg
Package Level 1 EAN	6417019338569

Technical

Conventional Free-air Thermal Current (I_{th})	$\Theta = 40\text{ °C } 1000\text{ A}$
Conventional Thermal Current (I_{the})	Fully Enclosed 1000 A
Degree of Protection	Front IP00
Distance Between Phases	Phase distance 140 mm

Handle Color	Black
Handle Type	Handle and shaft included
Mechanical Durability	6000
Mounting Type	Base mounting
Number of Poles	3P
Operating Mode	Front
Pollution Degree	3
Position of Line Terminals	Top In - Bottom Out Bottom In - Top Out
Power Loss	at Rated Operating Conditions per Pole 19 W
Rated Conditional Short-Circuit Current (I_{nc})	(1250 A fuse, 415 V) 80 kA (1250 A fuse, 500 V) 100 kA
Rated Impulse Withstand Voltage (U_{imp})	12 kV
Rated Insulation Voltage (U_i)	acc. to IEC/EN 60664-1 1000 V
Rated Operational Current AC-21A (I_e)	(380 ... 415 V) 1000 A (500 V) 1000 A (690 V) 1000 A
Rated Operational Current AC-22A (I_e)	(380 ... 415 V) 1000 A (500 V) 1000 A (690 V) 1000 A
Rated Operational Current AC-23A (I_e)	(380 ... 415 V) 1000 A (500 V) 1000 A (690 V) 1000 A
Rated Operational Power AC-23A (P_e)	(400 ... 415 V) 560 kW (500 V) 710 kW (690 V) 1000 kW
Rated Operational Voltage	Main Circuit 1000 V
Rated Short-Circuit Making Capacity (I_{cm})	(690 V) 110 kA
Rated Short-time Withstand Current Low Voltage (I_{cw})	for 1 s 50 kA
Special Functions	Wide phase distance 140
Standards	IEC 60947-3
Switches Operating Mechanism	Mechanism at the End of the Switch 03 (Left Side)
Terminal Type	Lug terminals
Terminal Width	50 mm
Tightening Torque	acc. IEC 60947-1 50 ... 75 N·m

Technical UL/CSA

Tightening Torque	acc. IEC 60947-1 50 ... 75 N·m
-------------------	--------------------------------

Certificates and Declarations

A2L Certificate - IEC	1SCC301338D0201
ATEX Certificate	No certification needed
Declaration of Conformity - CE	1SCC301155D2704
DNV GL Certificate	1SCC301184D0203
UL Certificate	No certification needed
VDE Certificate	No certification needed

External Classifications and Standards

Object Classification Code	Q
ETIM 9	EC000216 - Switch disconnecter (low voltage)

ETIM 10	EC000216 - Switch disconnecter (AC)
UNSPSC	39122221
eClass	V11.1 : 27371403
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
E-Number (Finland)	3661608

Categories

Low Voltage Products and Systems → Switches → Switch Disconnectors

