

Eaton 248233

Catalog Number: 248233

Eaton Distribution parts. Fuse switch-disconnector, 63A, 2p

General specifications



Product Name	Catalog Number
Eaton Distribution parts	248233
EAN	Product Length/Depth
4015082482336	88 mm
Product Height	Product Width
77 mm	54 mm
Product Weight	Compliances
0.224 kg	RoHS conform

Product specifications

Type

Fuse material

Special features

Standard empty

Suitable for fuses, utilisation

class gG (gL), aM

Current coding through fuse

set

sealable

Infeed possible from both

sides

Amperage Rating

63 A

Frame

Standard front dimension: 45 mm

Pollution degree

3

Creepage resistance

CTI 600

Equipment heat dissipation, current-dependent

1 W

Rated operational voltage (Ue) - max

400 V

Rated short-circuit making capacity up to 690 V, 50/60 Hz

50 kA

Rated uninterrupted current (Iu)

63 A

Static heat dissipation, non-current-dependent

0 W

Terminals

Lift terminals

Voltage rating at AC

400 V AC

Voltage rating at DC

250 V DC

Number of poles

Resources

Declarations of conformity

[DA-DC-03_Z-SLS_NEOZ](#)

[DA-DC-03_Z-S](#)

[DA-DC-03_Z-S_SC_SB](#)

Drawings

[eaton-dimensions-mas-sls.jpg](#)

[eaton-wiring-diagram-sls-cek-2p.jpg](#)

[1220DRW-18](#)

[eaton-mcb-dimensions-1220dim-15.eps](#)

mCAD model

[eaton-248233-3d-model.stp](#)

[eaton-248233-drawing.dwg](#)

Two-pole

Rated impulse withstand voltage (U_{imp})

6 kV

Degree of protection

IP20

Switching category

AC 22 B, DC 21 B

Ambient operating temperature - max

60 °C

Ambient operating temperature - min

-25 °C

Current heat loss per contact at I_e

0.5 W

Enclosure width

86 mm

Heat dissipation capacity

0 W

Heat dissipation per contact with fuse link at I_e

6.6 W

Heat dissipation per pole, current-dependent

0 W

Construction size

D02

Functions

Fuse switch-disconnector Z-SL.../NEOZ/...

Overvoltage category

III

IV

Fuse cartridge

D02, D01

Mounting method

Quick attachment for top-hat rail IEC/EN 60715

Rated operation current (I_e)

63 A

Voltage rating

400 V

Flammability characteristics (UL)

V0, glow-wire test 960 °C (UL94)

Mounting width

27 mm per pole (1.5 space units)

Terminal capacity (solid cable)

1.5 mm² - 35 mm²

Rated operational current for specified heat dissipation (In)

63 A



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia