

Terminal block, Linergy TR, grey, 2.5mm², push-in type, knife disconnect, 2 points, set of 50

NSYTRP22SC

EAN Code: 3606480533358

Price: 8,70 EUR

Main

Range	Linergy	
product name	Linergy TR	
Product or component type	Terminal block	
Device short name	TRP	
Terminal block type	Blade disconnect	
Terminal block level	1	
Mounting mode	Clip-on	
Nominal cross section	2.5 mm²	
Length	62 mm	
Colour	Grey	
Quantity per set	Set of 50	

Complementary

Width	5.2 mm	
Height	36.5 mm	
Connections - terminals	1 x push-in: upstream 1 x push-in: downstream	
number of connections	2	
Connection position	Тор	
Number of measurement input	2	
Cable cross section	0.142.5 mm², flexible without cable end 0.144 mm², solid	
Wire stripping length	10 mm	
Tool type	Disconnection: flat screwdriver Connection: without tool	
[Ue] rated operational voltage	300 V CSA 300 V UL 400 V conforming to EN/IEC 60947-7-1	
[In] rated current	20 A conforming to EN/IEC 60947-7-1 20 A UL 20 A CSA	
Material	Polyamide 6/6: insulating case	
Dielectric loss	0.01 at 1 MHz conforming to IEC 60250 0.01 at 1 MHz conforming to VDE 0303-T4	

Rates duty January 2016

Dielectric constant	3.7 at 1 MHz	
	3.7 at 1 M□2	
Resistivity	10000 M Ω .m conforming to IEC 60093	
	10000 MΩ.m conforming to VDE 0303-T30	
Surface resistance	1000 G Ω conforming to IEC 60093	
	1000 G Ω conforming to VDE 0303-T30	
Creep resistance	500 CTI (> 400 kB) conforming to IEC 60093	
	500 CTI (> 400 kB) conforming to VDE 0303-T30	
Flame retardance	V0, thickness0.8 mm conforming to UL 94	
Net weight	9.2 g	
Range compatibility	PrismaSeT G	
	PrismaSeT P	
	PrismaSet HD	
	PrismaSeT Pack 250	
	PanelSeT	
	Mureva	
	TeSys	
Product compatibility	Spacial enclosures	
Environment		
Product certifications	VDE	
i ioddol dei tilloations	GL	
	GL COA	

Product certifications	VDE GL CSA UL	
Dielectric strength	1000 V conforming to IEC 60243-1	
Ambient air temperature for operation	-40130 °C conforming to IEC 60216-1 -40130 °C conforming to VDE 0304-T21	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	7.0 cm
Package 1 Length	27.0 cm
Package 1 Weight	9.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	50
Package 2 Height	5.0 cm
Package 2 Width	7.0 cm
Package 2 Length	27.0 cm
Package 2 Weight	508.0 g



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	5
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
Halogen content performance	Halogen free plastic parts product

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No