

product description

XR-300 media module

SCALANCE X accessory, Media module MM991-2LH+, 2x 100 Mbit/s SC-ports optical; single-mode optical up to max. 70 km.



interfaces	
number of electrical/optical connections / for network components or terminal equipment / maximum	2
number of optical interfaces / for network components or terminal equipment / maximum	2
number of 100 Mbit/s SC ports / for multimode / integrated	2
design of the optical interface / for network components or terminal equipment	SC
wavelength / of the optical interface	1550 nm; Single-mode
connectable optical power relative to 1 mW <ul style="list-style-type: none"> • of the transmitter output / minimum • of the transmitter output / maximum • of the receiver input / maximum 	-5 dB 0 dB -3 dB
optical sensitivity relating to 1 mW / of the receiver input / minimum	-34 dB
attenuation factor / of the FOC transmission link / minimum necessary	3 dB
range / at the optical interface / depending on the optical fiber used	12 ... 70 km
ambient conditions	
ambient temperature <ul style="list-style-type: none"> • during operation • during storage • during transport 	-40 ... +60 °C -40 ... +85 °C -40 ... +85 °C
relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	Media module
width	60 mm
height	22 mm
depth	100 mm
net weight	0.08 kg
fastening method <ul style="list-style-type: none"> • installation in media module slot 	latched Yes
standards, specifications, approvals	
standard <ul style="list-style-type: none"> • for FM • for hazardous zone • for safety / from CSA and UL 	FM3611: Class 1, Division 2, Group A, B, C, D / T4, Class 1, Zone 2, Group IIC, T4 EN 60079-0: 2006, EN60079-15: 2005, II 3 G Ex nA II T4, KEMA 07 ATEX 0145 X UL 60950-1, CSA C22.2 No. 60950-1

<ul style="list-style-type: none"> • for hazardous zone / from CSA and UL • for emitted interference • for interference immunity 	UL 1604 and UL 2279-15 (Hazardous Location), CSA C22.2 No. 213-M1987, Class 1 / Division 2 / Group A, B, C, D / T4, Class 1 / Zone 2 / Group IIC / T4 EN 61000-6-4:2007 (Class A) EN 61000-6-2:2005
certificate of suitability <ul style="list-style-type: none"> • CE marking • C-Tick • KC approval • CCC / for hazardous zone according to GB standard • CCC / for hazardous zone according to GB standard / as marking 	EN 61000-6-2:2005, EN 61000-6-4:2007 Yes Yes Yes Yes; GB3836.1, GB3836.8 Ex nA IIC T4 Gc
MTBF	105 a
further information / internet links	
internet link <ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Image database • to website: CAx-Download-Manager • to website: Industry Online Support 	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com

last modified:

11/9/2023 