

Eaton 191580

Catalog Number: 191580

Eaton Moeller series NZM - Molded Case Circuit Breaker. NZM3 PXR20 circuit breaker, 220A, 3p, withdrawable unit, N, 3

General specifications



Product Name	Catalog Number
Eaton Moeller series NZM - Molded case circuit breaker	191580
	EAN 4015081920921
Product Length/Depth	Product Height
260 mm	346 mm
Product Width	Product Weight
185 mm	17.887 kg
Compliances	Certifications
RoHS conform	IEC/EN 60947 IEC

Product specifications

Type

Circuit breaker

Special features

IEC/EN 60947-2 with characteristic conforming to IEC/EN 60947-4-1 with phase failure sensitivity
The circuit-breaker fulfills all requirements for AC-3 switching category.

R.m.s. value measurement and “thermal memory”
Adjustable time delay setting to overcome current peaks I_r at $6 \times I_r$ also infinity (without overload releases)

All AC-3 rating data applies to direct switching by the circuit-breaker under normal operating conditions. If, for example, a contactor takes over AC-3 switching under normal operating conditions, the full rated uninterrupted current applies to the circuit-breaker, $I_n = I_u$.

Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn})
Rated current = rated uninterrupted current: 220 A
Terminal capacity hint: Up to 240 mm² can be connected depending on the cable manufacturer.

Application

Use in unearthed supply systems at 690 V

Amperage Rating

220 A

Resources

Brochures

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

Characteristic curve

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-029.eps](#)

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-015.eps](#)

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-011.eps](#)

Declarations of conformity

[DA-DC-03_N3](#)

Drawings

[eaton-circuit-breaker-nzm-mccb-dimensions-020.eps](#)

[eaton-circuit-breaker-switch-nzm-mccb-dimensions-016.eps](#)

[eaton-general-ie-ready-dilm-contactor-standards.eps](#)

Installation instructions

[eaton-circuit-breaker-basic-unit-bg3-il012100zu.pdf](#)

Installation videos

[The new digital NZM Range](#)

[Introduction of the new digital circuit breaker NZM](#)

mCAD model

[DA-CD-nzm3_xave](#)

[DA-CS-nzm3_xave](#)

Technical data sheets

[eaton-nzm-technical-information-sheet](#)

Voltage rating

690 V - 690 V

Circuit breaker frame type

NZM3

Accessories required

NZM3-XAVS

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Fitted with:

Thermal protection

Pollution degree

3

Mounting Method

Built-in device slide-in technique (withdrawable)

Withdrawable

Climatic proofing

Damp heat, cyclic, to IEC 60068-2-30

Damp heat, constant, to IEC 60068-2-78

Equipment heat dissipation, current-dependent

14.52 W

Utilization category

A (IEC/EN 60947-2)

Isolation

300 V AC (between the auxiliary contacts)

500 V AC (between auxiliary contacts and main contacts)

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-25 °C

Ambient storage temperature - max

70 °C

Ambient storage temperature - min

40 °C

Protection against direct contact

Finger and back-of-hand proof to VDE 0106 part 100

Rated insulation voltage (Ui)

690 V

Rated operating power at AC-3, 230 V

55 kW

Rated operating power at AC-3, 400 V

110 kW

Switch off technique

Electronic

Degree of protection

IP20

IP20 (basic degree of protection, in the operating controls area)

Direction of incoming supply

As required

Electrical connection type of main circuit

Other

Lifespan, mechanical

15000 operations

Overvoltage category

III

Rated operational current

196 A (400 V AC-3)

Degree of protection (IP), front side

IP66 (with door coupling rotary handle)

IP40 (with insulating surround)

Degree of protection (terminations)

IP10 (tunnel terminal)

IP00 (terminations, phase isolator and strip terminal)

Number of poles

Three-pole

Terminal capacity (copper strip)

Max. 10 segments of 24 mm x 1 mm + 5 segments of 24 mm x 1 mm at box terminal

Max. 10 segments of 32 mm x 1 mm + 5 segments of 32 mm x 1 mm at rear-side connection (punched)

Min. 6 segments of 16 mm x 0.8 mm at box terminal

Min. 6 segments of 16 mm x 0.8 mm at rear-side connection (punched)

10 segments of 50 mm x 1 mm (2x) at rear-side width extension

Max. 8 segments of 24 mm x 1 mm (2x) at box terminal

Lifespan, electrical

2000 operations at 415 V AC-3

5000 operations at 400 V AC-1

2000 operations at 690 V AC-3

3000 operations at 690 V AC-1

5000 operations at 415 V AC-1

2000 operations at 400 V AC-3

Functions

Phase failure sensitive

Motor protection

Shock resistance

20 g (half-sinusoidal shock 20 ms)

Rated operational current for specified heat dissipation (I_n)

220 A

Rated short-time withstand current (t = 0.3 s)

3.3 kA

Rated short-time withstand current (t = 1 s)

3.3 kA

Short-circuit release non-delayed setting - max

3960 A

Short-circuit release non-delayed setting - min

440 A

Handle type

Rocker lever

Instantaneous current setting (I_i) - max

18 A

Instantaneous current setting (I_i) - min

2 A

Number of operations per hour - max

60

Overload current setting (Ir) - max

220 A

Overload current setting (Ir) - min

88 A

Rated short-circuit breaking capacity Ics (IEC/EN 60947) at 230 V, 50/60 Hz

85 kA

Rated short-circuit breaking capacity Ics (IEC/EN 60947) at 400/415 V, 50/60 Hz

235 kA

Rated short-circuit breaking capacity Ics (IEC/EN 60947) at 440 V, 50/60 Hz

235 kA

Rated short-circuit breaking capacity Ics (IEC/EN 60947) at 525 V, 50/60 Hz

13 kA

Rated short-circuit breaking capacity Ics (IEC/EN 60947) at 690 V, 50/60 Hz

5 kA

Standard terminals

Screw terminal

Optional terminals

Box terminal. Connection on rear. Tunnel terminal

Release system

Electronic release

Short-circuit total breaktime

< 10 ms

Terminal capacity (aluminum solid conductor/cable)

16 mm² (1x) at tunnel terminal

Terminal capacity (aluminum stranded conductor/cable)

50 mm² - 240 mm² (1x) at 2-hole tunnel terminal

50 mm² - 240 mm² (2x) at 2-hole tunnel terminal

25 mm² - 185 mm² (1x) at tunnel terminal

Terminal capacity (control cable)

0.75 mm² - 2.5 mm² (1x)

0.75 mm² - 1.5 mm² (2x)

Terminal capacity (copper busbar)

Max. 10 mm x 50 mm (2x) at rear-side width extension

Min. 20 mm x 5 mm direct at switch rear-side connection

M10 at rear-side screw connection

Max. 30 mm x 10 mm + 30 mm x 5 mm direct at switch rear-side connection

Terminal capacity (copper solid conductor/cable)

300 mm² (2x) at rear-side width extension

16 mm² (1x) direct at switch rear-side connection

16 mm² (2x) at box terminal

16 mm² (1x) at tunnel terminal

16 mm² (2x) direct at switch rear-side connection

Terminal capacity (copper stranded conductor/cable)

16 mm² - 185 mm² (1x) at 1-hole tunnel terminal

25 mm² - 120 mm² (2x) at box terminal

25 mm² - 240 mm² (2x) direct at switch rear-side connection

25 mm² - 240 mm² (1x) direct at switch rear-side connection

35 mm² - 240 mm² (1x) at box terminal

Rated short-circuit breaking capacity I_{cu} (IEC/EN 60947) at 400/415 V, 50/60 Hz

235 kA

Rated short-circuit making capacity I_{cm} at 400/415 V, 50/60 Hz

105 kA

Rated short-circuit making capacity I_{cm} at 440 V, 50/60 Hz

74 kA

Rated short-circuit making capacity I_{cm} at 525 V, 50/60 Hz

53 kA

Rated short-circuit making capacity I_{cm} at 690 V, 50/60 Hz

40 kA

Rated short-circuit making capacity I_{cm} at 240 V, 50/60 Hz

187 kA

Rated impulse withstand voltage (U_{imp}) at auxiliary contacts

6000 V

Rated impulse withstand voltage (U_{imp}) at main contacts

8000 V



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia